

128, av. du Maréchal-de-Lattre-de-Tassigny - 87045 LIMOGES Cedex
Tel: 0 (+33) 5 55 06 87 87 - Fax: 0 (+33) 5 55 06 88 88
www.legrand.com

Salbei™
Socket outlets


Cat. No(s): 7 671 14/15/16/17/18 - 7 672 14/15/16/17/18 - 7 673 14/15/16/17/18 7 674 14/15/16/17/18 - 7 675 14/15/16/17/18 - 7 676 14/15/16/17/18 7 677 14/15/16/17/18 - 7 678 14/15/16/17/18 - 7 679 14/15/16/17/18



7 679 15



7 679 16



7 679 18

1. USE

Standards of socket outlets 16 A - 250 V~.
Flush-mounting or surface-mounting.
Fixing with screws and/or with claws.

2. RANGE

GERMAN STANDARD


2 P+E socket without shutter Supplied with cover plate and support frame To be equipped with plate	White Aluminium Anthracite Ivory Champagne Matt Gold Pink Smoked Grey White Pearl	7 671 14 7 672 14 7 673 14 7 674 14 7 675 14 7 676 14 7 677 14 7 678 14 7 679 14
2 P+E socket shuttered Supplied with cover plate and support frame To be equipped with plate	White Aluminium Anthracite Ivory Champagne Matt Gold Pink Smoked Grey White Pearl	7 671 15 7 672 15 7 673 15 7 674 15 7 675 15 7 676 15 7 677 15 7 678 15 7 679 15
2 x 2 P+E compact socket outlet without shutter Installation in 1-gang flush-mounting box Supplied complete with plate Allows you to replace 1 socket with 2 sockets without changing the flush-mounting box	White Aluminium Anthracite Ivory Champagne Matt Gold Pink Smoked Grey White Pearl	7 671 16 7 672 16 7 673 16 7 674 16 7 675 16 7 676 16 7 677 16 7 678 16 7 679 16
2 P+E socket outlet with flap cover, shuttered Supplied with cover plate and support frame To be equipped with plate	White Aluminium Anthracite Ivory Champagne Matt Gold Pink Smoked Grey White Pearl	7 671 18 7 672 18 7 673 18 7 674 18 7 675 18 7 676 18 7 677 18 7 678 18 7 679 18

2. RANGE *(continued)*

FRANCO-BELGIAN STANDARD

2 P+E socket shuttered Supplied with cover plate and support frame To be equipped with plate	White Aluminium Anthracite Ivory Champagne Matt Gold Pink Smoked Grey White Pearl	7 671 17 7 672 17 7 673 17 7 674 17 7 675 17 7 676 17 7 677 17 7 678 17 7 679 17

3. DIMENSIONS (mm)



References	A	B	C	D
2 P+E socket outlets 7 6xx 14/15/17	76	76	44.5	13.5
2 x 2 P+E compact socket outlets 7 6xx 16	104	86	51.5	22.5
2 P+E socket outlets with flap 7 6xx 18	76	76	49	18

4. CONNECTION

Type of terminals: with screws
Terminal capacity: 2 x 2.5 mm^2
Stripping length : - 9 mm for 2 P+E socket outlets
- 13 mm for double socket outlets 2 x 2 P+E
Screwdriver: Posidrive 1, Philips 1, flat 4 mm.

5. TECHNICAL CHARACTERISTICS

■ **5.1 Mechanical characteristics**
Protection against solid bodies and liquids: IP 31
Protection against impact: IK 04

■ **5.2 Material characteristics**
Polyglass appearance
Material: - Plate ABS
- Socket cover plate: PC
- Halogen free
- UV resistant

Material of the support: - PC grey RAL 7037 + 10 % glass fiber
- Halogen free

Self-extinguishing:
+ 850° C / 30 s for insulating parts holding live parts in place
+ 650° C / 30 s for other parts made of insulating materials.

■ **5.3 Electrical characteristics**
Voltage: 250 V~
Current: 16 A
Frequency: 50/60 Hz

■ **5.4 Climatic characteristics**
Storage temperature: - 10° C to + 70° C
Use temperature: - 5° C to + 35° C

6. MAINTENANCE

Surface cleaning with a cloth.
Do not use: acetone, tar remover, trichloroethylene.

Maintenance with the following products: Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, Window-cleaning products.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing.
Refer to e. catalogue.