

Shaver sockets

Cat. No(s): N4177 - NT4177 - L4177 - N4177/127 - NT4177/127 - L4177/127



N4177

1. USE

Shaver socket 2P, protected against overloads and direct short-circuits. Suitable for use with European et American 2-pin plugs.

The mechanism is supplied with rocker plate, to be equipped with support frame and plate.


2. GAMME

SHAVER SOCKETS		References
	Shaver socket with insulating transformer Input voltage 230 Vac 50/60 Hz Output voltage 115/230 Vac 20 VA 3 modules	□ N4177 ■ N4177 ■ N4177
	Shaver socket with insulating transformer Input voltage 127 Vac 50/60 Hz Output voltage 115/230 Vac 20 VA 3 modules	□ N4177V127 ■ N4177/127 ■ N4177/127

Colour code:

- □White
- Tech
- Anthracite

3. OVERALL DIMENSIONS (mm)



4. CONNECTION

Screw clamps:

Stripping length, rigid or flexible cables: 11 mm

5. TECHNICAL CHARACTERISTICS

■ 5.1 Protection index

Penetration by solid bodies/liquid: IP 21 D Impact test: IK 04

■ 5.2 Material characteristics

Material: Polycarbonate

Halogen free.

UV resistant.

Self-extinguishing:

- $+\,850^{\circ}\,\text{C}\,/\,30\,\text{s}$ for insulating parts holding live parts in place.
- $+\,650^{\circ}\,\text{C}\,/\,30\,\text{s}$ for other parts made of insulating materials.

■ 5.3 Electrical characteristics

Voltage: 250 VAC

■ 5.4 Climatic characteristics

Storage and operating temperatures: - 5° C to + 35° C

6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing.