


MyHOME® Play Radio dimmer controls

Cat. No(s): 0 672 29 - 0 746 89 - 7 520 80



0 672 29


1. USE

Wireless control for ON/OFF dimming function.
 Used to send a command to one or more radio receiver switches.
 Can be used as a two-way switch or to control a group.
 Can be combined with other wiring accessory products in a multi-gang unit.
 For fixing directly on the wall without a flush-mounting box.
 Remote control format.

2. RANGE

	Description	Colour	Cat. No.
	Céline control supplied with support To be fitted with a Céline cover plate and a Céline plate	-	0 672 29
	Mosaic control supplied with cover plate and support To be fitted with a plate	White	0 746 89
	Valena control supplied with support To be fitted with a Valena cover plate and a Valena plate	-	7 520 80

3. OVERALL DIMENSIONS (mm)



Cat. Nos.	A	B	C
0 672 29	74	74	9
0 746 89	74	74	11
7 520 80	75	75	9

4. CONNECTION

No connections (battery powered).

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact test: IK 04
 Penetration by solid bodies/liquid: - IP 40, product assembled
 - IP 20, without rocker

■ 5.2 Material characteristics

- Halogen-free
 - UV resistant
 Rocker plate material:
 - 0 746 89: PC white RAL 9003
 Material of the mechanism with support:
 - 7 520 80: PC reinforced with 10% glass

Self-extinguishing:

+ 850° C/30 s for insulating parts holding live parts in place
 + 650° C/30 s for other parts made of insulating materials

5. TECHNICAL CHARACTERISTICS *(continued)*

■ 5.3 Electrical characteristics

Powered by a CR2032 - 3 V lithium battery (supplied)
2.4 GHz Radiofrequency band (16 channels) - Byte rate: 250 KB/s
Self healing MESH network with high security level (AES128) according to IEEE 802.15.4 (LR-WPAN) standard.

■ 5.4 Climatic characteristics

Storage and operating temperatures: + 5° C to + 45° C

6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover or trichloroethylene.

Maintenance with the following products: hexane (EN 60669-1), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10% or window-cleaning products.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

The plates must not be painted.

7. STANDARDS AND APPROVALS

Compliance with installation and manufacturing standards.
Refer to e-catalogue.