


Valena™ 2 P+E socket outlets - IP 44 French standard Cat. No(s): 7 741 21 - 7 742 21



1. USE

Waterproof socket outlets, French standard. Mechanisms supplied with:


- Support
- Cover plate

To be equipped with plate.

2. RANGE

Description	lvory	White
2 P+E socket with shutters and flap cover	7 741 21	7 742 21

3. OVERALL DIMENSIONS (mm)



4. CONNECTION

Screw terminals Capacity: 2 x 2.5 mm² Stripping length: 10 mm Compatible flexible or rigid cables.

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against solid bodies and liquids: IP 44 Protection against impact: IK 04

■ 5.2 Material characteristics

Colour: - White RAL 9003 - Ivory RAL 1013

Material: - Membrane: PP

- Cover: PC (transparent)
- Cover plate (of the socket outlet): PC
- Halogen free
- UV resistant

Support: Zinc plated steel

Self-extinguishing:

- +850° C / 30 s for insulating parts holding live parts in place
- $+650^{\circ}$ C / 30 s for other parts made of insulating materials.

■ 5.3 Electrical characteristics

Voltage: 250 V~ Current: 16 A Frequency: 50/60 Hz

■ 5.4 Climatic characteristics

Storage and usage temperature: - 5° C to + 40° C

6. MAINTENANCE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistance to the following cleaning substances:

- Hexane
- Methylated spirit
- Soapy water
- Diluted amonia
- Diluted pure bleach 10%
- Glass cleaning product (Ethanol 1%, Butylglycol 6%)

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing. Refer to e. catalogue.