




Mosaic™

Socket for DLP trunking, monting with support Franco-Belgian standard

Cat. No(s): 0 773 01/02/03/04/21/22/23/24 0 792 22/23







0 773 01

0 773 02 0 773 03

1. DESCRIPTION

Socket outlets with shutters, with connection at both sides, for mounting on DLP trunking in conjunction with supports. Install one socket by support frame.

2. RANGE

2 P+E socket outlets - 2 modules

○White	0 773 01
Red tamperproof	0 773 21

2 x 2 P+E socket outlets - 4 modules

- X - I I - DOCKET OUT	iets imodules	
	○ White ● Red tamperproof ● Aluminium	0 773 02 0 773 22 0 792 22


3 x 2 P+ E socket outlets - 6 modules

○ White	0 773 03 0 773 23
Aluminium	0 792 23

3 x 2 P+ E socket outlets - 8 modules



3. OVERALL DIMENSIONS (mm)



Catalogue numbers	Α	В	C
0 773 01/21	45	90	41
0 773 02/22 - 0 792 22	45	135	41
0 773 03/23 - 0 792 23	45	180	41
0 773 04/24	45	225	41

4. CONNECTION

Type of terminals: automatic Number of terminals: 6 Terminal capacity: 2 x 2.5 mm² Stripping length: 10 mm

Note: Marking of phase (right spindle) by a white point.

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact tests: IK 04

Protection against solid bodies and liquids: IP 40

■ 5.2 Material characteristics

Base: ABS Cover plate: PC Halogen free UV resistant

 ${\sf Self-extinguishing:}$

- $+\ 850^{\circ}\,\text{C}\,/\ 30\,\text{s}$ for insulating parts holding live parts in place
- + 650° C / 30 s for other parts made of insulating materials.

■ 5.3 Electrical characteristics

Voltage: 250 V~ Current:16 A

■ 5.4 Climatic characteristics

Storage and use temperature: - 15° C to + 70° C

6. MAINTENANCE

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

Mosaic™ Socket for DLP trunking, monting with support Franco-Belgian standard

7. ACCESSORIES **Tamperproof insert** Fixes directly onto the 2P+E plug of 0 502 99 the appliance to be connected to the tamperproof socket. Cable end fitting Prevents tension on the connection between 0 898 07 the wire and socket if the cable is pulled. Supports 85 mm 65 mm 2 modules 0 109 52 0 109 92 4 modules 0 109 54 0 109 94 6 modules 0 109 56 0 109 96 0 109 98 8 modules 0 109 58

8. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing. Refer to e. catalogue.

Technical data sheet: F02096EN/00 Updated: