




Mosaic™

Socket for DLP trunking, monting with support Franco-Belgian standard

Cat. No(s): 0 773 31/32/33/34/41/42/43/44/81/82/83/84 6 744 27/29







0 773 33

0 773 31 0 773 32

1. DESCRIPTION


Socket outlets with shutters, with connection at both sides, for mounting on DLP trunking in conjunction with supports. Install one socket by support frame.

2. RANGE


2 P+E socket outlets - 2 modules

	○ White Red tamperproof	0 773 31 0 773 41
	○ White Supplied with support 65 mm	0 773 81


2 x 2 P+E socket outlets - 4 modules




3 x 2 P+ E socket outlets - 6 modules



4 x 2 P+ E socket outlets - 8 modules



3. OVERALL DIMENSIONS (mm)



Catalogue numbers	Α	В	С
0 773 31/41 - 0 773 81	45	71	41
0 773 81	45	71	41
0 773 32/42 - 6 744 27	45	116	41
0 773 82	45	116	41
0 773 33/43 - 6 744 29	45	161	41
0 773 83	45	161	41
0 773 34/44	45	206	41
0 773 84	45	206	41
	_	•	

4. CONNECTION

Type of terminals: with screws Number of terminals: 6 Terminal capacity: 2 x 2.5 mm² Stripping length: 10 mm

Socket for DLP trunking, monting with support Franco-Belgian standard

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact tests: IK 04

Protection against solid bodies and liquids: IP 40

■ 5.2 Material characteristics

Base: ABS

Cover plate: PC

Halogen free

UV resistant

Self-extinguishing:

- +850° C / 30 s for insulating parts holding live parts in place
- $+650^{\circ}$ C / 30 s for other parts made of insulating materials.

■ 5.3 Electrical characteristics

Voltage: 250 V~

Current:16 A

■ 5.4 Climatic characteristics

Storage and use temperature: - 15° C to + 70° C

6. MAINTENANCE

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

7. ACCESSORIES

Détrompeur



Fixes directly onto the 2P+E plug of the appliance to be connected to the tamperproof socket.

0 502 99

Cable end fitting



Prevents tension on the connection between the wire and socket if the cable is pulled.

0 898 07

Supports		65 mm	85 mm
	2 modules	0 109 52	0 109 92
	4 modules	0 109 54	0 109 94
	6 modules	0 109 56	0 109 96
	8 modules	0 109 58	0 109 98

8. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing. Refer to e. catalogue.

Technical data sheet: F02097EN/00 Updated: Created: 12/05/20