


Valena Life[™]-Valena[™] NMATIC-TV/R/SAT/SAT sockets

Cat. Nos: 7 530 56 - 7 548 10/11/12




1. USE


TV/R/SAT/SAT sockets: for terrestrial and satellite installation with individual demodulator; they can be used to receive digital programmes (satellite channels, etc.).

2. RANGE

| Description | Mechanism only | Cover plate only | | | |
|---------------------|----------------|------------------|----------|-----------|--|
| | | White | lvory | Aluminium | |
| TV/R/SAT/SAT socket | 7 530 56 | 7 548 10 | 7 548 11 | 7 548 12 | |


3. DIMENSIONS (mm)






| Cat. Nos. | Α | В | С | D |
|-----------|------|------|------|-----|
| 7 530 56 | 74.7 | 74.7 | 27.6 | 9.8 |

4. CONNECTION



5. WIRING PRECAUTIONS



To prevent loss of impedance and a subsequent deterioration in performance caused by deformation of the coaxial cable, use the largest possible bending radius.



A signal booster must be used with connecting and terminal sockets to compensate for the losses generated by this technique.

Cat. Nos: 7 530 56 - 7 548 10/11/12

6. TECHNICAL CHARACTERISTICS

■ 6.1 Mechanical characteristics

Protection against solid bodies and liquids: IP 21 Protection against impacts: IK 04

■ 6.2 Material characteristics

Casing: Poly gloss appearance

Colour: - White RAL 903

- Ivory RAL 113

- Aluminium

Material: - Plate: ABS/PC

Cover plate: ABSPrinted circuit: FR4

- Zero halogen

- UV resistant

Motor: Zamac cover/Zamac steel box/steel plugs and screws

■ 6.3 Electrical characteristics

- Male TV connector Ø 9.52 mm
- Female "F" screw-type connector Ø 9.4 mm
- Female "R" connector Ø 9.52 mm

- Frequency bands: TV: 5 - 68/120 - 862 MHz

R: 87.5 - 108 MHz SAT1: 950 - 2400 MHz SAT2: 950 - 2400 MHz

- Characteristic impedance: 75 Ohm

■ 6.4 Climate characteristics

Storage and operating temperature: -5°C to +35°C

7. PERFORMANCE

Testing in progress.

8. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products: Hexane (EN 60669-1), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.

9. STANDARDS AND APPROVALS

- EN 50083-2
- EN 50083-4