
128, av. du Maréchal-de-Lattre-de-Tassigny - 87045 LIMOGES Cedex Tel: 0 (+33) 5 55 06 87 87 - Fax: 0 (+33) 5 55 06 88 88 www.legrand.com

Cat. No(s): 0 671 24/26/28

Céliane™ Pre-wired socket outlets Franco-Belgian standard




1. USE


Pre-wired socket outlets, allow depending on the coverplate associated, to realize Surface or standard power outlets.

2. RANGE

Description	References	
Double socket 2 x 2 P+E pre-wired. To be mounted on support Cat. No 0 802 52 with a plate 2 gang	0 671 24	
Triple socket 3 x 2 P+E pre-wired To be mounted on support Cat. No 0 802 53 with a plate 3 gang	0 671 26	
Compact quadruple socket 4 x 2 P+E pre-wired. To be mounted on support Cat. No 0 802 53 with a special plate 6/8 modules	0 671 28	

3. OVERALL DIMENSIONS (mm)





3. OVERALL DIMENSIONS (mm) (continued)

References	A	В	С	D
0 671 24	45	116	42	8.5
0 671 26	45	187	42	8.5
0 671 28	45	180	42	8.5

4. CONNECTION

Type of terminals: with automatic color coding Number of terminals: 3 inputs, 3 outputs Terminal capacity: 2 x 2.5 mm² Stripping length: 12 mm

5. TECHNICAL CHARACTERISTICS

5.1 Mechanical characteristics

Impact test: IK 04 Penetration by solid bodies/liquid: IP 40

5.2 Material characteristics

Polycarbonate Halogen free

Self-extinguishing:

+ 850° C / 30 s for insulating parts holding live parts in place. + 650° C / 30 s for other parts made of insulating materials

■ 5.3 Electrical characteristics

Current: 16 A Voltage: 250 V~

5.4 Climatic characteristics

Storage temperature: - 10° C to + 70° C Use temperature: - 5° C to 50° C

6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards. See e-catalogue.