

128, av. du Maréchal-de-Lattre-de-Tassigny - 87045 LIMOGES Cedex - France
Tel: 0 (+33) 5 55 06 87 87 - Fax: 0 (+33) 5 55 06 88 88
www.legrand.com

Salbei™
Covers and accessories

Cat. No(s): 7 673 31/32/33/34/35/41/42/43/44/45/51/52/53/54/55/61/62/63/64/65/71/72/73/74/75/81/82/83/84/85
7 675 31/32/33/34/35/41/42/43/44/45/51/52/53/54/55/61/62/63/64/65/71/72/73/74/75
7 671 90/91 - 7 672 90/91 - 7 673 90/91 - 7 674 90/91 - 7 675 90/91 - 7 676 90/91 - 7 677 90/91 - 7 678 90/91 - 7 679 90/91



7 675 31





7 675 32

1. USE


Plates for Salbei 1-gang, 2-gang, 3-gang, 4-gang 5-gang and 6-gang wiring accessories.

2. RANGE

1-gang plates


	White	7 673 31
	Ivory	7 673 41
	Aluminium	7 673 51
	Anthracite	7 673 61
	Champagne	7 673 71
	Wood	7 673 81
	Dark Wood	7 675 31
	White Pearl	7 675 41
	Smoked Grey	7 675 51
	Matt Gold	7 675 61
	Pink	7 675 71
Plate with label-holder	White	7 671 90
	Aluminium	7 672 90
	Anthracite	7 673 90
	Ivory	7 674 90
	Champagne	7 675 90
	Matt Gold	7 676 90
	Pink	7 677 90
	Smoked Grey	7 678 90
	White Pearl	7 679 90

2-gang plates - 71 mm spacing - horizontal and vertical


	White	7 673 32
	Ivory	7 673 42
	Aluminium	7 673 52
	Anthracite	7 673 62
	Champagne	7 673 72
	Wood	7 673 82
	Dark Wood	7 675 32
	White Pearl	7 675 42
	Smoked Grey	7 675 52
	Matt Gold	7 675 62
	Pink	7 675 72

2. RANGE *(continued)*


3-gang plates - 71 mm spacing - horizontal and vertical

	White	7 673 33
	Ivory	7 673 43
	Aluminium	7 673 53
	Anthracite	7 673 63
	Champagne	7 673 73
	Wood	7 673 83
	Dark Wood	7 675 33
	White Pearl	7 675 43
	Smoked Grey	7 675 53
	Matt Gold	7 675 63
	Pink	7 675 73


4-gang plates - 71 mm spacing - horizontal and vertical

	White	7 673 34
	Ivory	7 673 44
	Aluminium	7 673 54
	Anthracite	7 673 64
	Champagne	7 673 74
	Wood	7 673 84
	Dark Wood	7 675 34
	White Pearl	7 675 44
	Smoked Grey	7 675 54
	Matt Gold	7 675 64
	Pink	7 675 74


5-gang plates - 71 mm spacing - horizontal and vertical

	White	7 673 35
	Ivory	7 673 45
	Aluminium	7 673 55
	Anthracite	7 673 65
	Champagne	7 673 75
	Wood	7 673 85
	Dark Wood	7 675 35
	White Pearl	7 675 45
	Smoked Grey	7 675 55
	Matt Gold	7 675 65
	Pink	7 675 75

6-gang plates - 71 mm spacing - horizontal and vertical

	White	7 671 91
	Aluminium	7 672 91
	Anthracite	7 673 91
	Ivory	7 674 91
	Champagne	7 675 91
	Matt Gold	7 676 91
	Pink	7 677 91
	Smoked Grey	7 678 91
	White Pearl	7 679 91

3. OVERALL DIMENSIONS (mm)



	A	B	C
1-gang	86	86	10.5
2-gang 71 mm fixing centres	86	157	10.5
3-gang 71 mm fixing centres	86	228	10.5
4-gang 71 mm fixing centres	86	299	10.5
5-gang 71 mm fixing centres	86	370	10.5
6-gang 71 mm fixing centres	86	441	10.5

4. TECHNICAL CHARACTERISTICS

■ **4.1 Mechanical characteristics**
Protection against impact: IK 04

■ **4.2 Material characteristics**
Polyglass appearance
Material: - ABS
- Halogen-free
- UV resistant
Self-extinguishing: + 650° C / 30 s

■ **4.3 Climatic characteristics**
Storage temperature: - 10° C to + 70° C
Use temperature: - 5° C to + 35° C

5. CLEANING

Clean the surface with a cloth.
Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Caution: An initial test is required for the use of other special maintenance products.

The plates should not be painted.