

128, av. du Maréchal-de-Lattre-de-Tassigny - 87045 LIMOGES Cedex - France
Tel: 0 (+33) 5 55 06 87 87 - Fax: 0 (+33) 5 55 06 88 88
www.legrand.com

Salbei™
Push-buttons and roller blinds

Cat. No(s): 7 671 05/09/68/69 - 7 672 05/09/67/68/69 - 7 673 05/09/67/68/69 - 7 674 05/09/68/69 7 675 05/09/67/68/69 - 7 676 05/09/67/68/69 - 7 677 05/09/67/68/69 - 7 678 05/09/67/68/69 7 679 05/09/67/68/69



7 671 05



7 671 68


1. USE


Control mechanisms supplied with rockers and support frames.
To be fitted with one-gang or multi-gang plates.
Flush or surface mounting.
Fixing with screws and/or claws.

2. RANGE

Description	White	Aluminium	Anthracite	Ivory	Champagne	Matt Gold	Pink	Smoked Grey	White Pearl
Push-buttons NO-NC	7 671 05	7 672 05	7 673 05	7 674 05	7 675 05	7 676 05	7 677 05	7 678 05	7 679 05
Illuminated push-buttons NO-NC	-	7 672 67	7 673 67	-	7 675 67	7 676 67	7 677 67	7 678 67	7 679 67
Double push-buttons NO-NC	7 671 68	7 672 68	7 673 68	7 674 68	7 675 68	7 676 68	7 677 68	7 678 68	7 679 68
Roller blind - Switches	7 671 09	7 672 09	7 673 09	7 674 09	7 675 09	7 676 09	7 677 09	7 678 09	7 679 09
Roller blind push-buttons	7 671 69	7 672 69	7 673 69	7 674 69	7 675 69	7 676 69	7 677 69	7 678 69	7 679 69

3. OVERALL DIMENSIONS (mm)





A	B	C	D
76	76	45.5	14.5

4. CONNECTION

Screw terminals:
Terminal capacity: 2 x 2.5 mm²
Stripping length: 8 mm for Cat. Nos 7 67x 09/69

Automatic terminals:
Terminal capacity: 2 x 2.5 mm²
Stripping length: 13 mm for Cat. Nos 7 67x 05/07/67/68

Compatible with flexible or rigid cables.
Cable entries for the phase marked with red colour code.

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics
Impact tests: IK 04
Penetration by solid bodies/liquids: IP 20

■ 5.2 Material characteristics
Rocker: ABS
Mechanism housing: PC
Halogen free
UV resistant
Claws: steel

Material of the support:
- PC Grey RAL 7037
- PC Grey RAL 7037 + 10 % glass fiber for cat. No 7 67x 09

Self-extinguishing:
+ 850° C / 30 s for insulating parts holding live parts in place.
+ 650° C / 30 s for other parts made of insulating materials.

■ 5.3 Electrical characteristics
Voltage: 250 V~
Current: - 6 A for 7 67x 05/07/67/68/69
- 6 AX for 7 67x 09

■ 5.4 Climatic characteristics
Storage temperature: - 10° C to + 70° C
Use temperature: - 5° C to + 35° C

6. CLEANING

Clean the surface with a cloth.
Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistance to the following cleaning substances:
Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Diluted pure bleach 10%, Glass cleaning product.

Caution: An initial test is required for the use of other special maintenance products.

7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing.
See e.catalogue.