


Synergy™ **Double pole switches BS 45 A** Metalclad

Cat. No(s): 7 338 21



1. USE


45A double pole switches delivered complete for surface-mounting, to control fixed appliances eg. cooker ovens, showers or air-conditionning

Fixing with screws.

2. RANGE

Double pole switch	7 338 21
bouble pole strices	7 330 21

3. OVERALL DIMENSIONS (mm)



Cat. No	Α	В	С	D
7 338 21	146	86	48	12

4. CONNECTION

Type of terminals: with screws

Terminal capacity: 3 x 4 mm² - 2 x 6 mm² - 1 x 10 mm² - 1 x 16 mm²

Stripping length: L / N: 24 mm - E: 12 mm

Compatible with flexible or rigid cables

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact tests: IK 08

Penetration by solid bodies/liquids: IP 20

■ 5.2 Material characteristics

Rocker: PC - Color: Red

Front plate and surface monting back box: Grey epoxy coated steel Mechanism housing: PC - Color: Grey

Halogen free

UV resistant

Self-extinguishing:

- +850° C / 30 s for insulating parts holding live parts in place.
- $+650^{\circ}$ C / 30 s for other parts made of insulating materials.

■ 5.3 Electrical characteristics

Voltage: 250 V~ Current: 45 A Frequency: 50/60 Hz

■ 5.4 Climatic characteristics

Storage temperature: -10° C to $+70^{\circ}$ C Use temperature: -5° C to $+35^{\circ}$ C

6. CLEANING

Clean the surface with a cloth or soapy water.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Caution: An initial test is required for the use of other special maintenance products.

8. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing. See e.catalogue.