


Céliane™ Cat. No: 0 648 87

Connected mobile socket outlet 16 A French standard



1. USE

Connected mobile socket outlet which can be controlled by a wireless lighting control and/or remotely via your smartphone, tablet or computer.

Allow the control of the plugged devices and appliances.


Can be used to measure instantaneous and total consumption of the connected device, which can be viewed on the Home + Control app. Protection against electrical overload, for more safety.

Its receiver function allows the remote control of the socket outlet with a wireless remote switch and scene switches.

2. RANGE

Description	Graphite
Connected mobile socket outlet 2 P+E 16 A, equipped with	
child protection.	0 648 87
Equipped with ON/OFF button with indicator LED and RESET	
button (left side) to come back to factory mode.	


3. DIMENSIONS (mm)



4. CONNECTION

To be plugged on 2 P+E in wall socket outlet.

5. FUNCTION



6. TECHNICAL CHARACTERISTICS

■ 6.1 Mechanical characteristics

Protection against impacts: IK 04 Protection against solid bodies and/or liquids: IP 40

■ 6.2 Material characteristics

PC Graphite RAL 7016

Halogen-free

UV resistant

Self-extinguishing:

 850° C / 30 s for insulating parts holding live parts in place. 650° C / 30 s for the other insulating components.

■ 6.3 Electric characteristics

Voltage: 110/230 V~ Current: 16 A Power: 3680 W Frequency: 50/60 Hz Standby consumption: 0.1 mA

ZigBee radio technology 2.4 GHz to 2.4835 GHz

Power level: < 100 mW Range: 200 m of far field

10 m recommended between products indoor

■ 6.4 Climate characteristics

Storage temperature: 0° C to + 45° C Usage temperature: +5° C to + 45° C

Céliane[™] Cat. No: 0 648 87

Connected mobile socket outlet 16 A French standard

7. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products: Hexane (EN 60669-1), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.

The plates must not be painted.

8. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards. See e-catalogue.

The undersigned, LEGRAND, declares that the radio-electric equipment type (0 648 87) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website: ${\bf www.legrandoc.com}$