


Céliane™

Floor heating thermostat

Catalogue number: 0 674 05






1. USE

Thermostat for electric floor heating. Mechanisms to be equipped with finishes.


2. RANGE

Description	Cat. No.
Floor heating thermostat 230 VAC, with external sensor.	0 674 05

3. PREPARATION




4. OVERALL DIMENSIONS (mm)



5. CONNECTION

Tool: flat screwdriver 3.5 mm

Number of terminals: 6 Type of terminals: with screws Terminal capacity: 2 x 1.5 mm² flexible or rigid Stripping length: 6 mm



Floor heating thermostat

6. FUNCTION

The thermostat is equipped with a temperature sensor and an external floor sensor and provides changover relay depending on the ambient temperature.


The regulation is ensured by an algorithm (commutation cycle) thus ensuring a minimal temperature variation relative to the ambient temperature.


Setting range 10-30 °C by using the rotary knob.


A short press on the "select" button cycles between the modes comfort -> frost -> off -> comfort and so on.


A long press on the "select" button adjust the brightness of the LEDs.

Regulation Accuracy: < 0.5°C for a conventional installation and maximum charge of 8.4









7. TECHNICAL CHARACTERISTICS

■ 6.1 Index of protection

Protection against solid bodies and liquids: IP 21 Impact tests: IK 04

■ 6.2 Material characteristics

Polycarbonate

■ 6.3 Electrical characteristics

Self extinguishing: 850° C / 30 s Voltage: 230 VAC Frequency: 50/60 Hz

■ 6.4 Climatic characteristics

Storage temperature: - 10° C to + 70° C Cooling temperature: - 5° C to + 40° C

8. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing. Refer to e. catalogue.