


128, av. du Maréchal-de-Lattre-de-Tassigny - 87045 LIMOGES Cedex Tel.: 33(0)5 55 06 87 87 - Fax: 33(0)5 55 06 88 88 www.legrand.com

Valena[™] Life Connected 2-gang ON/OFF wireless control for lighting and sockets

Cat. Nos: 7 521 87 - 7 522 87 - 7 523 87 - 7 563 87



4. OPERATION

1. USE

Wireless control for 2 ON/OFF light functions or connected socket. Controls micromodule products, connected sockets and connected dimmer switches.

Can be used as a two-way switch or to control a lighting group.

Fixes directly on the wall or screws onto a flush-mounting box. Multi-gang versions can be combined with other wiring accessories.
Fits on a piece of furniture (movable).

Can control up to 2 x 20 micromodules, connected sockets, connected dimmer switches


2. RANGE

2-gang wireless lighting and socket control for an ON/OFF, dimmer, centralisation function. Supplied complete with battery.

With LED indicator (configuration) and RESET button (hidden) used to return to factory settings. Repositionable self-adhesive fixings supplied.

White	lvory	Alu	Black
7 521 87	7 522 87	7 523 87	7 563 87

3. DIMENSIONS (mm)



Short press: ON/OFF Long press: dimming + LED indicators: - useful during installation - when pressed, burst flash red if the battery power is low Short press: ON/OFF Long press: ON/OFF

RESET button used to return to factory settings

5. TECHNICAL CHARACTERISTICS

5.1 Mechanical characteristics

Protection against impacts: IK 02 Protection against solid bodies/liquids: IP 20 without plate or rocker plate IP 40 for assembled product

■ 5.2 Material characteristics

Plate: ABS Sub-plate: PC Rocker plate: ABS Mechanism with grid: Fibreglass-reinforced (10%) PC

Halogen-free UV-resistant

Self-extinguishing: 650°C/30 s

■ 5.3 Electrical characteristics

Powered by a CR2032 - 3 V lithium battery (supplied) Battery life: 8 years for 10 activations a day

ZigBee radio technology

Frequency bands: 2.4 GHz to 2.4835 GHz Power level: < 100 mW

5.4 Climate characteristics

Usage temperature: $+5^{\circ}C$ to $+45^{\circ}C$ Storage temperature: $0^{\circ}C$ to $+45^{\circ}C$

Valena[™] Life **Connected 2-gang ON/OFF wireless control** for lighting and sockets

6. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products: Hexane (EN 60669-1), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, windowcleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.

The plates must not be painted.

🚹 🌠 Take care to recycle the battery appropriately

7. ACCESSORIES

0 648 71: Repositionable adhesive for wireless control (x 4 supplied)

8. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (7 521 87 - 7 522 87 - 7 523 87 - 7 563 87) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website: www.legrandoc.com