


n o w


Socket outlet - Italian standards

Cat. No(s): KW4113 - KM4113 - KG4113 - KR4113 KW4180 - KM4180 - KG4180 - KR4180 KW4140A16 - KM4140A16 - KG4140A16 - KR4140A16 KW4140A16F - KM4140A16F - KG4140A16F - KR4140A16F









K4140A16F

K4140A16

1. USE

Socket outlets: Italia standards, Italian and German standards.

2. RANGE

ITALIA STANDARD	Cat. Nos.	Related Cover code
2 P+E 10 A 250 Vac socket - centre distance 19 mm shielded tulip contact Ø 4 mm	☐ KW4113 ■ KM4113 ■ KG4113 ■ KR4113	☐ KW02 ■ KM02 ■ KG02 ■ KR02
2 P+E 16 A 250 Vac socket - centre distance 19 mm and 26 mm - shieled tulip contacts - for plugs 2 P and 2 P+E 10 and 16 A	□ KW4180 ■ KM4180 ■ KG4180 ■ KR4180	☐ KW02 ■ KM02 ■ KG02 ■ KR02
ITALIAN AND GERMAN STANDARD	Cat. Nos.	Related Cover code
2 P+E 16 A 250 Vac socket - centre distance 19 mm and 26 mm in 2-centre configuration - protection tulip contacts; earth side contacts for German standards plugs; suitable for: 2 P and 2 P+E 10/16 A Italian standard plug, 2 P+E 16 A German standard plug	☐ KW4140A16 ■ KM4140A16 ■ KG4140A16 ■ KR4140A16	☐ KW03 ■ KM03 ■ KG03 ■ KR03
2 P+E 16 A 250 Vac flat socket - centre distance 19 mm and 26 mm in 2-centre configuration - protection tulip contacts; earth side contacts for German standards plugs; suitable for: 2 P and 2 P+E 10/16 A Italian standard plug, 2 P+E 16 A German standard plug	☐ KW4140A16F ■ KM4140A16F ■ KG4140A16F ■ KR4140A16F	☐ KW03 ■ KM03 ■ KG03 ■ KR03


Colours code:

□White

■ Sand ■ Black

Red

3. OVERALL DIMENSIONS (mm)



Wall surface reference
C
\

	Α	В	C*	D*
1 module	45	22	28	10
2 modules	45	45	32	10

^{*} Average overall dimensions depending of the standard.

4. CONNECTION

Screw clamps:

Stripping length, rigid or flexible cables: 9 mm

5. TECHNICAL CHARASTERISTICS

■ 5.1 Protection index

Penetration by solid bodies/liquid: IP 21 D Impact test: IK 04

■ 5.2 Material characteristics

Material: Polycarbonate

Colour: White, Sand, Black, Red

Halogen free.

UV resistant.

Self-extinguishing:

- +850° C / 30 s for insulating parts holding live parts in place.
- $+\ 650^{\circ}\ C\ /\ 30\ s$ for other parts made of insulating materials.

■ 5.3 Electrical characteristics

Voltage: 250 VAC Current: 10 or 16 A

■ 5.4 Climatic charasteristics:

Storage and operating temperatures: - 5° C to + 35° C

Technical data sheet: F02694EN/00 Updated: Created: 25/05/2018



Socket outlet - Italian standards

Cat. No(s): KW4113 - KM4113 - KG4113 - KR4113 KW4180 - KM4180 - KG4180 - KR4180 KW4140A16 - KM4140A16 - KG4140A16 - KR4140A16 KW4140A16F - KM4140A16F - KG4140A16F - KR4140A16F

6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

.....

7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufactoring. Refer to e.catalogue.