


Niloé™ Step Socket outlets - German Standard - IP44

Cat. No(s): 8 641 35



1. USE

Socket outlets with shutters.

Mechanisms supplied with protection cover.

To be equipped with plates one or several gangs.


Flush-mounting or surface-mounting.


Screw or claw fixing.

2. RANGE

Description	White
2 P+E socket outlet with flap cover IP 44	8 641 35

3. DIMENSIONS (mm)





Α	В	С	D
78.5	78.5	52.4	34.5

4. CONNECTION

Type of terminals: automatic Terminal capacity: 2 x 2.5 mm² Stripping length: 13 mm Compatible with flexible or rigid cables.

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against solid bodies and liquids: IP 44 Protection against mechanical impact: IK 04

■ 5.2 Material characteristics

Material: - Box of the mechanism: PC

- Rocker: ABS
- Halogen free
- UV resistant
- Claws: steel
- Protection cover: SEBS

Material of the support : - PC - Halogen free

Self-extinguishing:

- $+\,850^{\circ}\,\text{C}\,/\,30\,\text{s}$ for insulating parts holding live parts in place.
- $+\,650^{\circ}\,\text{C}\,/\,30\,\text{s}$ for other parts made of insulating materials.

■ 5.3 Electrical characteristics

Voltage: 250 V~ Current: 16 A Frequency: 50/60 Hz

■ 5.4 Climatic characteristics

Storage and use temperature: -5° C to $+35^{\circ}$ C

6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Maintenance with the following products:

Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, Window-cleaning products.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards. See e.catalogue.