


Modul'up™ Box for false ceiling Cat. No(s): 0 885 00



1. USE

Modul'up box pour false ceiling.

Allows you to put your installation in standby, connecting a DCL, connected DCL, spot or E27 base.


At the center point, can be used to suspend up to 25 kg with recovery from the back on the frame, securing faster center point by the use of the securing device.

Suitable for installation with blown wool and rolled wool.

2. RANGE

| Description | Reference |
|---|-----------|
| Modul'up box pour false ceiling. Drilling diameter 80 mm allowing easy search of ducs. Equipped with 2 inputs Ø 16/20 mm. | 0 885 00 |


3. DIMENSIONS (mm)



| Reference | ØΑ | В | С | D |
|-----------|----|----|----|----|
| 0 885 00 | 86 | 75 | 60 | 50 |

4. CONNECTION

Whitout tools or stripping Cable section: 3 x 1.5 mm² Conduit: 2 x (3 x 1.5 mm²)





5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against impacts: IK 04 Protection against solid bodies/liquids: IP 20

■ 5.2 Material characteristics

Casing: Black PC

Box: Yellow PP + Membrane: grey SEBS

End caps: PP + SEBS gray

Ring: grey PP

UV-resistance Halogen-free

Self-extinguishing:

 850° C/30 s for insulating components holding live parts in place 650° C/30 s for other insulating components

■ 5.3 Electrical characteristics

Voltage: 250 V~

Current: 6 A

■ 5.4 Climate characteristics

Storage temperature: -10°C to +70°C Usage temperature: -5°C to +35°C

6. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Caution: Always test before using special cleaning products.

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards. See e-catalogue.

8. ACCESSORIES

| 0 885 09 | Securing device allowing suspension up to 25 kg. Fast implementation by self-locking system. Avoid going back into the attic to finish installation. |
|----------|--|
| 0 885 08 | Hole saw Ø 79 mm With centering drill and spring Drilling < 30 mm |