



Mosaic[™] 2P+E Flush socket outlets French/Belgian standard

Cat. No(s): 0 771 11L - 0 771 81L - 0 791 21L 0 793 42





1. USE

Shuttered 2P+E Flush socket outlets.

Easy to clean and prevent accumulation of dirt.


Flush or surface-mounting.


For installation in flush-mounting box 40 mm deep (minimum recommended).

2. RANGE

Description	White	Aluminium	Matt black	
2P+E Flush - 2 modules	0 771 11L	0 793 42	0 791 21L	
2P+E Flush - 2 modules Product supplied complete	0 771 81L	-	-	

3. DIMENSIONS (mm)





Cat. Nos.	Α	В	C	D
0 771 11L - 0 792 21L - 0 793 42	45	45	38.5	8.5
0 771 81L	82	82	38.5	10

4. CONNECTION

Type of terminals: automatic Number of terminals: 3 inputs, 3 outputs Terminal capacity: 2 x 2.5 mm² Stripping length: 12 mm

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Penetration by solid/liquid matter: IP 41 for assembled product Impact resistance: IK 04

■ 5.2 Material characteristics

Mechanism casing: PC

Cover plate: White RAL 9003 ABS + PC

Painted glittery varnished aluminium ABS + PC Painted satin-finish Matt black RAL 9017 ABS + PC

Halogen-free

UV-resistant

Self-extinguishing:

 850° C/30 s for insulating components holding live parts in place. 650° C/30 s for other insulating components.

■ 5.3 Electrical characteristics

Current: 16 A Voltage: 250 V~

■ 5.4 Climate characteristics

Storage temperature: -10° C to $+70^{\circ}$ C Usage temperature: -5° C to $+35^{\circ}$ C

6. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistance to the following cleaning products: Hexane (NF C 61-314), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using other special cleaning products.

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards. See e-catalogue.