



# Niloé™ Step Push-buttons 6 A

Cat. No(s): 8 631 09/10 - 8 633 09/10 8 634 09/10 - 8 635 09/10






## 1. USE

Lighting controls mechanisms 6 A - 250 V~. Mechanisms supplied with protection cover. To be equipped with plates one or several gangs. Flush-mounting or surface-mounting. Screw or claw fixing.

# 2. RANGE

Description	White	White Aluminium Grey		Black	
One-gang push-button	8 631 09	8 633 09	8 634 09	8 635 09	
Illuminated one-gang push-button with bell symbol	8 631 10	8 633 10	8 634 10	8 635 10	

### 3. DIMENSIONS (mm)



References	Α	В	С	D
8 63X 09	75.0	75.0	44.5	21
8 63X 10	75.8	75.8	44.5	31

### 4. CONNECTION

Type of terminals: automatic Capacity: 2 x 2.5 mm<sup>2</sup> Flexible or rigid cables compatible

References	Stripping length (mm)
8 63X 09	42
8 63X 10	13

### **5. TECHNICAL CHARACTERISTICS**

#### ■ 5.1 Mechanical characteristics

Protection against solid bodies and liquids: IP 20 Protection against impact: IK 04

#### ■ 5.2 Material characteristics

Material: - Mechanism housing: PC

- Rocker plate: ABS
- Halogen free
- UV resistant
- Claws: steel

Material of the support: - PC + FV

- Halogen free

#### Self-extinguishing:

- + 850° C / 30 s for insulating parts holding live parts in place
- $+650^{\circ}$  C / 30 s for other parts made of insulating materials

### ■ 5.3 Electrical characteristics

Voltage: 250 V~

Current: 6 A

Frequency: 50/60 Hz

#### ■ 5.4 Climatic characteristics

Storage and use temperature:  $-5^{\circ}$  C to  $+35^{\circ}$  C

### **6. MAINTENANCE**

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Maintenance with the following products: Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, Window-cleaning products.

**Caution:** A preliminary test should be carried out if other specific cleaning products are to be used.

### 7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing. Refer to e. catalogue.