


128, av. du Maréchal-de-Lattre-de-Tassigny - 87045 LIMOGES Cedex Tel: 0 (+33) 5 55 06 87 87 - Fax: 0 (+33) 5 55 06 88 88 www.legrand.com

Niloé™ Socket outlets - German Standard - IP44




1. USE

Socket outlets with shutters. Supplied with protection cover. Flush or surface mounting. Screw or screw and claw mounting with claws. To be fitted with one-gang or multi-gang plates.

2. RANGE

Description	White	lvory
2 P+E socket outlet with shutters IP 44	7 645 31	7 646 31

3. DIMENSIONS (mm)



Α	В	с	D	E	F	G
86	86	75.8	75.8	50	30.1	92

4. CONNECTION

Type of terminals: screw Terminal capacity: 2 x 2.5 mm² Stripping length: 9 mm Compatible with flexible or rigid cables.

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against solid bodies and liquids: IP 44 Protection against mechanical impact: IK 04

5.2 Material characteristics

Material: - Box of the mechanism: PC

- Flap: ABS
- Halogen free
- UV resistant
- Claws: steel

Material of the support : - PC - Halogen free

Self-extinguishing:

- + 850° C / 30 s for insulating parts holding live parts in place.
- + 650° C / 30 s for other parts made of insulating materials.

5.3 Electrical characteristics

Voltage: 250 V~ Current: 16 A Frequency: 50/60 Hz

5.4 Climatic characteristics

Storage temperature: - 10° C to + 70° C Use temperature: - 5° C to + 35° C

6. CLEANING

Surface cleaning with a cloth. Do not use: acetone, tar remover, trichloroethylene.

Maintenance with the following products: Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, Window-cleaning products.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

cleaning products are to be used.

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards. See e.catalogue.