


Niloé™ Socket outlets - French Standard - IP44

Cat. No(s): 7 645 61 - 7 646 61




1. USE

Socket outlets without shutters.
Supplied with protection cover.
Flush or surface mounting.
Screw or screw and claw mounting with claws.
To be fitted with one-gang or multi-gang plates.

2. RANGE

Description	White	lvory	
2 P+E socket outlet without shutters IP 44	7 645 61	7 646 61	

3. DIMENSIONS (mm)



Α	В	С	D	E	F	G
86	86	75.8	75.8	47	30.1	92

4. CONNECTION

Type of terminals: screw Terminal capacity: 2 x 2.5 mm² Stripping length: 9 mm

Compatible with flexible or rigid cables.

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against solid bodies and liquids: IP 44 Protection against mechanical impact: IK 04

■ 5.2 Material characteristics

Material: - Box of the mechanism: PC

- Flap: ABS
- Halogen free
- UV resistant
- Claws: steel

Material of the support : - PC

- Halogen free

Self-extinguishing:

- $+850^{\circ}$ C / 30 s for insulating parts holding live parts in place.
- $+\,650^{\circ}\,\text{C}\,/\,30\,\text{s}$ for other parts made of insulating materials.

■ 5.3 Electrical characteristics

Voltage: 250 V~ Current: 16 A Frequency: 50/60 Hz

■ 5.4 Climatic characteristics

Storage temperature: - 10° C to + 70° C Use temperature: - 5° C to + 35° C

6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Maintenance with the following products:

Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, Window-cleaning products.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards. See e.catalogue.