


128, av. du Maréchal-de-Lattre-de-Tassigny - 87045 LIMOGES Cedex Tel: +33(0)5 55 06 87 87 - Fax: +33(0)5 55 06 88 88 www.legrand.com

Pocket remote control 4 scenarios



1. USAGE

Allows control of all connected wired controls (lights, appliances, roller shutters).


Requires the prior installation of a starter pack for connected installation or a Control modul.

With keychain hook.


2. RANGE

Description	Graphite
Connected poket remote control, 4 configurable scenarios. Supplied with battery. With LED indicator (configuration) and RESET button (hidden) used to return to factory settings.	0 676 95

3. DIMENSIONS (mm)



4. FONCTIONNEMENT



5. TECHNICAL CHARACTERISTICS

5.1 Mechanical characteristics

Protection against impacts: IK 02 Protection against solid bodies and liquids: IP 20

5.2 Material characteristics

Housing and front cover: ABS Halogen-free

UV resistant

■ 5.3 Electrical characteristics

Powered by a CR2032 - 3 V lithium battery (supplied) Battery life: 8 years for 10 activations a day

Frequency band: 2.4 to 2.44835 GHz Power level: < 100 mW

5.4 Climate characteristics

Usage temperature: $+5^{\circ}C$ to $+45^{\circ}C$ Storage temperature: $0^{\circ}C$ to $+45^{\circ}C$

6. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products: Hexane (EN 60669-1), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, windowcleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.

 \wedge X

Take care to recycle the battery appropriately

7. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (0 676 95) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website: www.legrandoc.com.

Compliant with installation and manufacturing standards. See e.catalogue.