


Niloé^{TM sélection}
Push-buttons 6 A

Cat. No(s): 7 621 07/13 - 7 622 07/13 7 623 07/13 - 7 624 07/13



1. USE


Lighting controls mechanisms 6 A - 250 V~. Mechanisms supplied with protection cover. To be equipped with plates one or several gangs. Flush-mounting or surface-mounting. Screw or claw fixing.

2. RANGE

Description	Aluminium	Antharcite	Smoked grey	Pearl
One-gang changeover push-button	7 621 07	7 622 07	7 623 07	7 624 07
Illuminated one-gang changeover push-button with bell symbol	7 621 13	7 622 13	7 623 13	7 624 13



3. DIMENSIONS (mm)



References	Α	В	С	D
7 62X 07	75.8	75.8	45.1	31
7 62X 13				

4. CONNECTION

Type of terminals: automatic Capacity: 2 x 2.5 mm² Flexible or rigid cables compatible

References	Stripping length (mm)		
7 62X 07	4.5		
7 62X 13	13		

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against solid bodies and liquids: IP 20 Protection against impact: IK 04

■ 5.2 Material characteristics

Material: - Mechanism housing: PC

- Rocker plate: ABS
- Halogen free
- UV resistant
- Claws: steel

Material of the support: - PC

- Halogen free

Self-extinguishing:

- +850° C / 30 s for insulating parts holding live parts in place
- $+650^{\circ}\,\text{C}\,/\,30\,\text{s}$ for other parts made of insulating materials

■ 5.3 Electrical characteristics

Voltage: 250 V~

Current: 6 A

Frequency: 50/60 Hz

■ 5.4 Climatic characteristics

Storage and use temperature: -5° C to $+35^{\circ}$ C

6. MAINTENANCE

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Maintenance with the following products: Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, Window-cleaning products.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing. Refer to e. catalogue.

Created: 16/10/2020 **L7 legrand**