


TV/R/SAT/SAT socket

Mosaic<sup>™</sup> Cat. No(s): 0 787 94



## 1. USE

TV/R/SAT/SAT: for receiving TV, Radio and SAT1 / SAT2 Satellite signals). UHD compatible (Ultra High Definition).

Class A shielded star sockets LTE Ready (4G protected).

Recommended coaxial cables 17/19 VATC.

Two cable entries.


Can be flush mounted in a box min. 40 mm deep.

To be equipped with plate.


### 2. RANGE

Designation	White
TV/R/SAT/SAT socket - 2 modules	0 787 94


# 3. DIMENSIONS (mm)



# 4. CONNECTION



# **5. WIRING PRECAUTIONS**





By restricting deformation of the coaxial cable, the rear connection avoids impedance discontinuity, thereby sustaining performance.

# **6. TECHNICAL CHARACTERISTICS**

#### ■ 6.1 Mechanical characteristics

Protection against impacts: IK 03

Protection against solid/bodies and liquids: IP 21

Cable resistance: 120 N

#### ■ 6.2 Material characteritics

Cover plate: White ABS RAL 9003

Halogen-free UV-resistant

Motor: Box: Zamac

Cover: Zamac

Pin: Bronze

Screws: Steel

Self-extinguishing:

 $850^{\circ}\text{C/30}$  s for insulating parts holding live parts in place.  $650^{\circ}\text{C/30}$  s for other parts made of insulating materials.

### ■ 6.3 Electrical characteristics

Male connector Ø 9.52 mm (TV)

Female connector (Radio)

Female F screw-type connector (SAT)

Impedance: 75 ohm

Class A shielding efficiency (class A shielding is necessary to prevent interference caused by using new 3 and 4 G phone signals, as these unwantedsignals can result in pixellation on screen or adversely affect the sound track).

Frequency bands: TV: 5-68/120-862 MHz

R: 87.5-108 MHz SAT1: 950-2400 MHz SAT2: 5-2400 MHz

#### ■ 6.4 Climate characteristics

Storage temperature:  $-10^{\circ}$ C to  $+70^{\circ}$ C Usage temperature:  $-5^{\circ}$ C to  $+35^{\circ}$ C

### 7. CLEANING

Surface cleaning with a cloth.

Do not use acetone, tar remover, trichloroethylene.

Resistant to the following products: Hexane (NF C 61-314), Methylated spirit, soapy water, diluted ammonia, bleach diluted to 10 %, window-cleaning products, pre-impregnated wipes.

**Caution:** Always test before using special cleaning products.

### 8. STANDARDS AND APPROVALS

Technical data sheet: F03268EN/00

 $\label{lem:compliant} \mbox{Compliant with installation and manufacturing standards.} \\ \mbox{See e-catalogue}.$ 

## 9. PERFORMANCES

