


Arteor™ USB Type C+C charger - 15 W

Cat. No(s): 5 716 92/93/94/95




1. USE

For recharging portable devices such as phones, smartphones, MP3 or MP4, loudspeakers, watches, game consoles, powerbanks.

2. RANGE

15 W USB charger	White	Magnesium	Champagne	Soft Alu
USB Type C+C charger	5 716 92	5 716 93	5 716 94	5 716 95

3. OVERALL DIMENSIONS (mm)



4. CONNECTION

Type of terminals: with screws

Terminal capacity: 1 x 2.5 mm² - 2 x 1.5 mm²

Stripping length: 6 mm Circuit Breaker: MAX. 16 A **Necessary safety precautions:**



Switch OFF the power at the main circuit breaker. Make sure that the power is OFF besfore continuing with the installation.

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact tests: IK 04

Penetration by solid bodies/liquid: IP 40

■ 5.2 Material characteristics

Base: PC V-0 class

Cover: painted PC V-0 class

Self-extinguishing:

 850°C/30 s for insulating components holding live parts in place. 650°C/30 s for other insulating components.

■ 5.3 Electrical characteristics

All values listed below are measured at an ambient temperature of + 20° and after 30 minutes of operation.

Nominal input voltage	100-240 V~		
Nominal input frequency	50/60 Hz		
Nominal input current	0.5 A		
Max. nominal output current	3.0 A		
Max. output power	15 W		
Nominal output voltage	5.0 V≔		
Average efficiency in active mode	85 %		
Stand-by power consumption	< 0.1 W		
Consumption class without load and average level of efficiency: Level VI			
Protection class	II - Low voltage		

Note: To optimize the charging time of your device, ensure turn it offduring the charging phase.

■ 5.4 Climate characteristics

Storage temperature: -20°C to +70°C Operating temperature: +5°C to +40°C

6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Caution: Always test before using other special cleaning products

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards. See e.catalogue