



Suno™ Lighting controls Cat. No(s): 7 21X 02/12





# 1. USE


Lighting control mechanisms. to be equipped with plates one or several gangs. Flush-mounting or surface-mounting.

Screw or claw fixing.


### 2. RANGE

Description	White	Aluminum	Black
2-POLE SWITCH	7 211 02	7 213 02	7 214 02
2-POLE SWITCH INDICATOR	7 211 12	7 213 12	7 214 12

# 3. DISMANTLING



# 4. DIMENSIONS (mm)



References	Α	В	С	D
7 21X 02/12	72,9	72,9	40,8	12,5

# 5. CONNECTION

Screw terminals

Capacity:

2 x 4 mm2

Stripping length:

10 mm

Flexible or rigid cables compatible

### **6. TECHNICAL CHARACTERISTICS**

#### ■ 6.1 Mechanical characteristics

Protection against solid bodies and liquids: IP 20

Protection against impact: IK 04

#### ■ 6.2 Material characteristics

Polygloss appearance

Colour molded:

- White RAL 9003 - Ivory RAL 1013

Matt colour painted: - Aluminum RAL 9023

- Black RAL 9017

#### Material:

- Plate ABS
- Socket covers: Polycarbonate
- Halogen-free
- UV resistant

### Self-extinguishing:

 $850^{\circ}\text{C/30}$  s for insulating components holding live parts in place  $650^{\circ}\text{C/30}$  s for other insulating components

# ■ 6.3 Electrical characteristics

Voltage: 250 V~ Current: 10 AX

Max. power for self-ballasted lamps: 100 W

Frequency: 50/60 Hz

# ■ 6.4 Climate characteristics

Usage temperature: -  $5^{\circ}$ C to +  $35^{\circ}$ C Storage temperature: -  $10^{\circ}$ C to +  $70^{\circ}$ C

### 7. MAINTENANCE

Surface cleaning with a cloth.

Do not use:

Acetone, tar remover, trichloroethylene.

Maintenance with the following products:

Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, Window-cleaning products, Pre-Impregnated-wipes.

Caution: Always test before using other special cleaning products.

### 8. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards. See e-catalogue.

Technical data sheet: F03650EN/00 Updated: 30/05/2022