


Suno™

Socket outlets - without earthing contact 16A

Cat. No(s): 7 21X 19, 7 21X 33




1. USE


Socket outlets with or without shutters. Flush-mounting.
Screw and/or claw fixing.

2. RANGE					
SOCKET OUTLETS WITHOUT SHUTTERS:	White	lvory	Aluminum	Black	
2P sockets screw terminal	7 211 33	7 212 33	7 213 33	7 214 33	
SOCKET OUTLETS WITH SHUTTERS:	White	lvory	Aluminum	Black	
2P sockets screw terminal	7 211 19	-	7 213 19	7 214 19	

3. DISMANTLING



3. DIMENSIONS (mm)



References	Α	В	С	D
7 21X 19/33	72,9	72,9	37,6	9,8

5. CONNECTION

Flexible or rigid cables compatible.

TYPE OF TERMINALS:		
Screw terminal Tightening torque: 0,8 Nm	7 21X 19	7 21X 33

Terminal capacity:

6 X 2.5mm²

Stripping length:

10mm

Screwdriver:

Posidirve 1, flat 4mm

6. TECHNICAL CHARACTERISTICS

■ 6.1 Mechanical characteristics

Protection against solid bodies and liquids:

IP20	7 21X 19	7 21X 33

Protection against impact: IK04

■ 6.2 Material characteristics

Polygloss appearance

Colour molded:

- White RAL 9003 - Ivory RAL 1013

Matt colour painted:

- Aluminum RAL 9023 - Black RAL 9017

Material:

- Plate ABS
- Socket covers: Polycarbonate
- Halogen-free
- UV resistant

Self-extinguishing:

 850°C/30 s for installing components holding live parts in place 650°C/30 s for other insulating components

■ 6.3 Electrical characteristics


Voltage: 250 V~ Current: 16 A Frequency: 50/60 Hz

■ 6.4 Climatic characteristics

Usage temperature: -5° C to $+35^{\circ}$ C Storage temperature: -10° C to $+70^{\circ}$ C

■ 6.5 Support


Material of support: -Metal Angular adjusting:



■ 6.6 Fixing with claws

Number of turns to open the claws:

- 58 mm > 2,1 turns
- 65 mm > 2,75 turns



■ 6.7 Cover fixing

Fixing with screw maximum 1 Nm tightening

7. MAINTENANCE

Surface cleaning with a cloth.

Do not use:

Acetone, tar remover, trichlorothylene.

Maintenance with the following products:

Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, Window-cleaning products.

Caution: Always test before using other special cleaning products.

8. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards. Refer to e-catalogue.