


Eloe™ Senses Shaver socket






1. USE

Device for the supply of electric shavers requiring either a 230V or 120V supply and having a power consumption not exceeding 20VA. Accepts the following types of plug: BS, Euro, US, Australian and Chinese. (Supplied with M3.5 screws for Flush mounting or surface mounting BS boxes.)

2. RANGE

Designation	White	
2 GANG SHAVER SOCKET	6 180 18	

3. DIMENSIONS (mm)



References	А	В	С	D
6 180 18	149.5	86	52.5	40.9

Minimum depth of the box>48 mm

4. CONNECTION

Types of terminals: auto terminal Terminal capacity: 2 X 1.5 mm² 2 X 2.5 mm²

Recommended stripping length: 13 mm

5. TECHNICAL CHARACTERISTICS

5.1 Material characteristics

Plate: PC Frame: PC Base: PC

Self-extinguishing:

- + 850° C / 30 s for insulating parts holding live parts in place
- + 650° C / 30 s for other parts made of insulating materials

5.2 Electrical characteristics

Transformer: primary and secondary 230 V - 120/230 V

Frequency: 50/60 Hz Power: 20VA Max.

5.3 Climatic characteristics

Storage temperatures: -10 $^{\circ}$ C to +70 $^{\circ}$ C Operating temperatures: -5°C to +35°C

5.4 Mechanical characteristics

Impact test: IK04

Protection against solids & liquids: IP24

6. CLEANING

Surface cleaning with a soft, slightly damp cloth. Do not use: acetone, tar remover, trichloroethylene

7. CONFORMITY - APPROVALS

Conform to BS EN 61558-2-5.

Created: 24/04/2022