


Céliane™

Wireless colour ambiance switch

Cat. No(s): 0 677 67/68/69 - 1 991 36/37




1. USE

Wireless switch to control multicolor smart lighting.
Controls any kind of Zigbee 3.0 certified bulbs and lighting (such as Ledvance, Smart + Zigbee, Philips HUE and many others).
Can be used as a two-way switch or to control a lighting group.
• Se fixe directement sur un mur ou se visse sur une boîte d'encastrement.
Multi-gang versions can be combined with other wiring accessories.
• Fits on a piece of furniture (movable).
Can control up to 20 connected zigbee 3.0 lights.

2. RANGE



Description	White	Titane	Graphite
Wireless switch for multicolor ambiance - 2 modules 3 ambiances (I - II - III) to select in Home + Control App. Supplied with battery. Equipped with an LED indicator (configuration) and a RESET button (hidden) used to return to factory settings. Repositionable self-adhesive fixings (supplied). To be equipped with finishing plate.	0 677 67	0 677 68	0 677 69
See description above. Product delivered complete (with finishing plate).	1 991 36	1 991 37	-

3. DIMENSIONS (mm)



Cat. Nos.	A	B	C
0 677 67/68/69	74	74	13
1 991 36/37	82	90	13

4. OPERATION



RESET button
used to return to factory settings

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against impacts: IK 02
Protection against solid bodies and/or liquids: IP 20
IP 40 mounted product

■ 5.2 Material characteristics

Mechanism casing with grid: Fibreglass-reinforced (10%) PC

Colour	White	Titane	Graphite
Rocker	ABS	Painted ABS	Painted ABS
Plate	ABS + PC	-	-

Halogen-free
UV-resistant

Self-extinguishing: 650°C/30 s

■ 5.3 Electrical characteristics

Powered by a CR2032 - 3 V lithium battery (supplied)
Battery life: 8 years for 10 activations a day

Zigbee radio technology

Frequency bands: 2.4 GHz to 2.4835 GHz
Power level: < 100 mW

■ 5.4 Climate characteristics

Usage temperature: +5°C to +45°C
Storage temperature: 0°C to +45°C

6. CARE

Clean the surface with a cloth.
Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products:
Hexane, methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.



Take care to recycle the battery appropriately.

7. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (0 677 67/68/69 - 1 991 36/37) complies with directive 2014/53/EU. The full text of the EU declaration of conformity is available on the following website: www.legrandoc.com