


Arteor™

# **Connected fan controller 4 speeds**

Cat. No(s): 5 742 48/49/50/51



### 1. USE

Connected fan controller 4 speeds. Controls any type of 230 V~ AC fan up to 100 W. Can be installed in place of an existing switch. Not compatible with DC fans.

## 2. RANGE


Fan controller for ON/OFF and fan speed regulation. Supplied with rocker plate.


Equipped with LED indicators (configuration/speed). Hidden reset button used to return to factory settings.

2 modules

White	Magnesium	Champagne	Soft Alu
5 742 48	5 742 49	5 742 50	5 742 51


# 3. DIMENSIONS (mm)






Α	В	С	D
45	45	42	9

### 4. OPERATION





## 5. CONNECTION

Type of terminals: with screws

Terminal capacity:  $1 \times 2.5 \text{ mm}^2 \text{ or } 2 \times 1.5 \text{ mm}^2$ 

Stripping length: 8 mm Screwdriver: 3.5 mm

### Cat. No(s): 5 742 48/49/50/51

# **Connected fan controller 4 speeds**

## **6. TECHNICAL CHARACTERISTICS**

#### ■ 6.1 Mechanical characteristics

Protection against impacts: IK 04

Protection against solid bodies and/or liquids: IP 20

#### ■ 6.2 Material characteristics

Mechanism casing: PC

Rocker plate: ABS White RAL 9003

Painted ABS Champagne, Magnesium, Soft Alu

Halogen-free UV-resistant

Self-extinguishing:

 $850^{\circ}\text{C/30}$  s for insulating components holding live part in place  $650^{\circ}\text{C}$  for other insulating components

#### ■ 6.3 Electrical characteristics

Voltage: 240 V~ Max. power: 100 W

Standby consumption: < 0.2 W

Frequency: 50/60 Hz

**ZigBee radio technology**: Frequency: 2.4 GHz to 2.4835 GHz

Power level: < 100 mW

### ■ 6.4 Climate characteristics

Storage temperature:  $0^{\circ}$ C to  $+ 45^{\circ}$ C Usage temperature:  $+5^{\circ}$ C to  $+ 45^{\circ}$ C

## 7. CLEANING

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products:

Hexane (EN 60669-1), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

**Caution:** Always test before using special cleaning products.

# 8. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (5 742 48/49/50/51) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website:  ${\bf www.legrandoc.com}$ 

Technical data sheet: F03843EN/00 Updated: Created: 19/12/2022