



# Plexo™ TV/R/SAT (DAB+) sockets

Cat. No(s): 0 695 54L - 0 695 58L 0 696 54L - 0 698 58L





### 1. USE

Waterproof equipment system intended for residential and professional technical locations (garages, cellars, car parks, workshops and industrial kitchens, etc.) as well as outdoor environments (terraces, gardens, campsites, etc.).

TV/R/SAT: allows reception of TV, Radio and Satellite signals.

Compatible with UHD (Ultra High Definition) television and DAB+ radio (Digital Audio Broadcasting).


Class A shielded star plug, 4G Lte compatible.

Recommended cable 17/19 VATC.

#### 2. RANGE


	References: Designations
Configurable	0 695 54L - 0 695 58L 0 696 54L - 0 698 58L

## 3. OVERALL DIMENSIONS (mm)





	Α	В	С	D
Configurable	70.5	70.5	47.7	-

## 4. CONNECTION



## 5. WIRING PRECAUTIONS





Connection from the rear of the socket reduces deformation of the coaxial cable, thus avoiding the risk of impedance loss and impaired performance.

## **6. TECHNICAL CHARACTERISTICS**

#### ■ 6.1 Mechanical characteristics

Protection against solid bodies and liquids: IP 55 Protection against impacts: IK 07 Cable resistance: 120 N: standard IEC 61169-24

#### ■ 6.2 Material characteristics

Material: Cover-plate: ABS Mechanism casing: PC Support: PC Claws: Steel

Halogen-free **UV-resistant** 

Motor: - Box: Zamac

- Cover: Zamac - Pin: Bronze

- Screws: Steel

Self-extinguishing: 650°C/30 s

## ■ 6.3 Electrical characteristics

- Impedance: 75 Ohm

- Male connector Ø 9.52 mm (TV)

- Class A shielding efficiency (class A shielding is necessary to prevent interference caused by using new 3 and 4 G phone signals, as these unwanted signals can result in pixellation on screen or adversely affect the sound track).

- Frequency bands: TV: 5-68 / 320-862 MHz R: 87,5-240 MHz SAT: 950-2400 MHz

UHD : passage des signaux d'amélioration :

WCG: Wide Color Gamut HDR: High Dynamic Range HFR: High Frame Rate

DAB+: AAC+ codec pass defined in the MPEG-4 part3 standard

- Low attenuation: <1.5 dB

Insulation resistance: standard IEC 61169-24

#### ■ 6.4 Climate characteristics

Storage temperature: -10°C to +70°C Use temperature: -5°C to +40°C

## 7. MAINTENANCE

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.


Maintenance with the following products: Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, Window-cleaning products.


**Caution:** Always test before using other special cleaning products.

## 8. STANDARDS AND APPROVALS

Technical data sheet: F03847EN/00

Compliant with installation and manufacturing standards Refer to e. catalogue.





Prises TV Radio DAB

