


PlexoTM

2P+E Schuko socket outlets

Cat. No(s): 0 695 70L/71L 0 696 39L/40L 0 697 00/30L/33L/67L/70L/71L/83L/99L 0 698 33L/34L/39L/59L/68L/69L/71L



1. USE


Weatherproof wiring accessory system for residential and professional plant rooms (garages, cellars, car parks, industrial workshops and kitchens) as well as outdoor environments (terraces, gardens, camp sites, etc). Socket outlets with protection eclips.

2. RANGE


	References
Configurable	0 695 70L/71L 0 696 39L/40L 0 697 00L 0 698 39L/71L
Surface-mounting complete	0 697 30L/33L/67L/70L/71L/83L/99L
Flush-mounting complete	0 698 33L/34L/59L/68L/69L

3. OVERALL DIMENSIONS (mm)

■ Configurable




■ Surface-mounting



3. OVERALL DIMENSIONS (mm) (continued)

■ Flush-mounting



	Α	В	С	D
Configurable	70.5	70.5	45.75	-
Surface-mounting	84.5	82	61.55	-
Flush-mounting	85.1	85.1	54.4	28.4

4. CONNECTION

Type of terminals: automatic

Terminal capacity: 1.5 mm² - 2.5 mm² (1 or 2 conductors)

Stripping length: 12 mm

5. TECHNICAL CHARACTERISTICS

■ 5.1 Protection index

Protection against solid bodies and liquids:

_ IP 55 with flap closed

_ IP 44 with flap open

Protection against impact: IK 08

■ 5.2 Material characteristics

Box, support: PP reinforced

Front plate, flap: ABS Entry gland, cover plate: PP + SEBS

Mechanism: PC

UV-resistant

Halogen-free

Resistance to salt spray: 7 days (168 h)

Self-extinguishing:

 $850^{\circ}\text{C}/30 \text{ s}$ for insulating components holding live parts in place.

650°C/30 s for other insulating components.

Plexo™ 2P+E Schuko socket outlets

Cat. No(s): 0 695 70L/71L 0 696 39L/40L 0 697 00/30L/33L/67L/70L/71L/83L/99L 0 698 33L/34L/39L/59L/68L/69L/71L

5. TECHNICAL CHARACTERISTICS (continued)

■ 5.3 Electrical characteristics

Voltage: 250 V~ Current: 16 A Frequency: 50 Hz

■ 5.4 Climate characteristics

Usage temperature: $-10^{\circ} \text{ à} + 40^{\circ} \text{ C}$ Storage temperature: -25° C à $+60^{\circ}$ C

6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Maintenance with the following products: Hexane (EN 60669-1),

Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, Window-cleaning products, Pre-saturated wipes.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing. Refer to e. catalogue.

Created: 08/10/2024 **L7 legrand**