


Plexo™ Relay command Cat. No(s): 0 697 37L/38L




1. USE

Waterproof equipment system intended for residential and professional technical locations (garages, cellars, car parks, workshops and industrial kitchens, etc.) as well as outdoor environments (terraces, gardens, campsites, etc.). Relay command mechanisms with key release.

2. RANGE

		References: Designations	
Surface- mounting complete		0 697 37L : Fireman stop relay command 2 NO contact	
		0 69738L : Rearming relay command 2 NO contact	

3. OVERALL DIMENSIONS (mm)



	Α	В	С	D
0 697 37L/38L	84.5	82	83.3	105.3

4. CONNECTION

Type of terminals: screw

Terminal capacity: 1.5 mm² - 2.5 mm² (1 or 2 conductors)

Stripping length: 8 mm

5. TECHNICAL CHARACTERISTICS

■ 5.1 Protection index

Protection against solid bodies and liquids: IP 55 Protection against impact: IK 07

■ 5.2 Material characteristics

Box, entry gland: PP + SEBS Support : PC + SEBS Mechanism: PC

UV-resistant

Halogen-free

Resistance to salt spray: 7 days (168 h)

Self-extinguishing:

 850°C/30 s for insulating components holding live parts in place. 650°C/30 s for other insulating components.

■ 5.3 Electrical characteristics

2 NO contacts with 10A breaking capacity at 250V~ 50/60Hz or 1.5A at 24V= $\,$

■ 5.4 Climate characteristics

Usage temperature: $-10^{\circ} \text{ à} + 40^{\circ} \text{ C}$ Storage temperature: $-25^{\circ} \text{ C à} + 60^{\circ} \text{ C}$

6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Maintenance with the following products: Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, Window-cleaning products, Pre-saturated wipes.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing. Refer to e. catalogue.