


Céliane™ LED lighting - Reading light

Cat. No(s): CB0270 - CN0270 - CT0270



1. USE


For specific directionnal lighting.
 To be mounted in a recessed box depth 40 mm minimum.

2. RANGE

Equipped with a flexible cable so the head can swivel.
 Has its own integrated on/off and dimming control (by continuous press).
 Supplied with cover plate. To be equipped with support frame and finishing plate.

White	Black	Titanium
CB0270	CN0270	CT0270

3. DIMENSIONS (mm)



A	B	C	D	Ø E	IE
45	45	32	330	53	-

4. CONNECTION

Terminal capacity: 2 x 1.5 mm² or 2 x 2.5 mm²
 Connection type: with screws
 Screwdriver: Flat 3 mm
 Stripping length: 8 mm
 Tightening torque: 0.5 Nm

5. TECHNICAL CHARACTERISTICS

5.1 Protection index

Penetration by solid bodies and/or liquid: IP 20
 Impact test: IK 04

5.2 Material characteristics

Material:
 Cover PC
 Diffuser: PC
 Painted cover, painted head reading light: ABS
 Flexible: steel


Halogen-free
 UV-resistant

Self-extinguishing:
 850°C/30 s for components holding live parts in place.
 650°C/30 s for other insulating components.

5.3 Electrical characteristics


Voltage: 230 V~
 Frequency: 50 Hz
 Current: 23 mA
 Luminous flux: 110 lm
 Power input: 3.3 W
 Color temperature: 3,000 K, neutral white
 Product tested to 40,000 operations switching ON and OFF.

5.4 Photoelectric characteristics



5.5 Climate characteristics

Storage temperature: -25°C to +45°C
 Usage temperature: -5°C to +35°C



6. CARE

Surface cleaning with a cloth.
Do not use: acetone, tar remover, trichloroethylene.

Caution: Always test before using other special cleaning products

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.
See e.catalogue.