


SEANOTM

Lighting controls 10 A/ 10 AX

Cat. No(s): 7 650 05/06/07/08/10/11/17/18




1. USE


Lighting controls mechanism 10 AX - 250 V \sim . Flush-mounting or surface-mounting. Screw and/or claw fixing.

2. RANGE

switch with automatic terminal	MECHANISM ONLY
10AX 2-way switch	7 650 06
10AX 2-way switch with neutral	7 650 10
10AX 2-way 2-gang switch	7 650 08
10AX 1-way 2-gang switch	7 650 05
10A changeover push-button	7 650 11
10A changeover push-button free contact	7 650 17
10A 2-way push-button	7 650 18
switch with screw terminal	MECHANISM ONLY
10AX Intermediate switch	7 650 07

3. DISMANTLING





SEANO[™] Lighting controls 10 A/ 10AX

5. CONNECTION

Flexible or rigid cables compatible.

Type of terminals

Automatic terminal Screw terminal

Tightening torque: 0,8 Nm

Terminal capacity:

2 x 2.5mm2/terminal

Stripping length:

7 650 05/06/08/10/11/17/18: 13mm 7 650 07: 10mm

Screwdriver:

Posidirve 1, Flat 4mm

6. TECHNICAL CHARACTERISTICS

■ 6.1 Mechanical characteristics

Protection against solid bodies and liquids: IP20 Protection against impact: IK04

■ 6.2 Material characteristics

Material:

- Rocker ABS
- Base: Polycarbonate
- Halogen-free
- UV resistant

Self-extinguishing:

 850°C/30 s for installing components holding live parts in place 650°C/30 s for other insulating components

■ 6.3 Electrical characteristics

Voltage: 250 V~ Current: 10 AX Frequency: 50/60 Hz


Max. power for self-ballasted lamps: 100W

■ 6.4 Climatic characteristics

Usage temperature: -5° C to $+35^{\circ}$ C Storage temperature: -10° C to $+70^{\circ}$ C

■ 6.5 Support


Material of support: -Metal Angular adjusting:



■ 6.6 Fixing with claws

Number of turns to open the claws:

- 58 mm > 2,1 turns
- 65 mm > 2,75 turns



Performance of double teeth claws: extraction resistance

7. MAINTENANCE

Surface cleaning with a cloth.

Do not use:

Acetone, tar remover, trichlorothylene.

Maintenance with the following products:

Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, Window-cleaning products.

.....

Caution: Always test before using other special cleaning products.

8. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards. Refer to e. catalogue..