


128, av. du Maréchal-de-Lattre-de-Tassigny - 87045 LIMOGES Cedex Tel: 0 (+33) 5 55 06 87 87 - Fax: 0 (+33) 5 55 06 88 88 www.legrand.com

SEANO<sup>™</sup> Control for opening with mechanical and electrical interlock


## Cat. No(s): 7 650 29/30




# 1. USE

Control mechanisms for roller shutters, blinds and awnings with mechanical and electrical interlock. Flush-mounting or surface-mounting. Screw and/or claw fixing.

2. RANGE	
Description	Mechanism Only
INTERLOCKED ROLLER BLIND SWITCH	7 650 29
INTERLOCKED ROLLER BLIND PUSH-BOTTON	7 650 30




# 4. DIMENSIONS (mm)



# 5. CONNECTION


Flexible or rigid cables compatible. TYPE OF TERMINALS: Auto terminal TERMINAL CAPACITY: 2 x 2.5mm2/terminal STRIPPING LENGTH: 13mm

### ■ 5.1 Push-button wiring (7 650 29)



# SEANO<sup>™</sup> Control for opening with mechanical and electrical interlock

#### ■ 5.2 Switch wiring (7 650 30)



### **6. TECHNICAL CHARACTERISTICS**

## ■ 6.1 Mechanical characteristics

Protection against solid bodies and liquids: IP20 Protection against impact: IK04

#### ■ 6.2 Material characteristics

- Material:
  - Plate ABS
  - Socket covers: Polycarbonate
  - Halogen-free
  - UV resistant

Self-extinguishing: 850°C/30 s for installing components holding live parts in place 650°C/30 s for other insulating components

### ■ 6.3 Electrical characteristics


Voltage: 250 V~ Current: 6 A for 7 65X 30 6 AX for 7 65X 29 Frequency: 50/60 Hz

#### ■ 6.4 Climatic characteristics

Usage temperature: -5°C to +35°C Storage temperature: -10°C to +70°C

### ■ 6.5 Support

Material of support: -Metal Angular adjusting:



# ■ 6.6 Fixing with claws

Number of turns to open the claws: - 58 mm > 2,1 turns

-65 mm > 2,75 turns



Performance of double teeth claws: extraction resistance:

# 7. MAINTENANCE

Surface cleaning with a cloth.

Do not use: Acetone, tar remover, trichlorothylene.

Maintenance with the following products: Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, Window-cleaning products.

Caution: Always test before using other special cleaning products.

## 8. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards. Refer to e-catalogue.