

## PENDANT U50 PG

Reference(s) : 348089 – 348090 – 348091 – 348092 – 348093 – 348094 – 348095 – 348096 – 348097 – 348098 – 348099



### 1 RANGE

Ref	Code	Matière Raw material	Norme Standard	Finition Coating	Norme standard	RAIL Epaisseur Thickness (mm / Inch)	L Longueur Length (mm / Inch)	Masse / Weight (KG / lb)
Pendant U50 L250 PG	348 092	S250GD Z275 MAC	EN 10346	GS	/	2 / 0,079"	256 / 10,08"	0,933 / 2,053
Pendant U50 L300 PG	348 093	S250GD Z275 MAC	EN 10346	GS	/	2 / 0,079"	306 / 12,05"	1,013 / 2,229
Pendant U50 L400 PG	348 094	S250GD Z275 MAC	EN 10346	GS	/	2 / 0,079"	406 / 15,98"	1,173 / 2,581
Pendant U50 L500 PG	348 095	S250GD Z275 MAC	EN 10346	GS	/	2 / 0,079"	506 / 19,92"	1,333 / 2,933
Pendant U50 L600 PG	348 096	S250GD Z275 MAC	EN 10346	GS	/	2 / 0,079"	606 / 23,85"	1,493 / 3,285
Pendant U50 L700 PG	348 097	S250GD Z275 MAC	EN 10346	GS	/	2 / 0,079"	706 / 27,79"	1,653 / 3,637
Pendant U50 L800 PG	348 098	S250GD Z275 MAC	EN 10346	GS	/	2 / 0,079"	806 / 31,73"	1,813 / 3,989
Pendant U50 L900 PG	348 099	S250GD Z275 MAC	EN 10346	GS	/	2 / 0,079"	906 / 35,69"	1,973 / 4,341
Pendant U50 L1000 PG	348 090	S250GD Z275 MAC	EN 10346	GS	/	2 / 0,079"	1006 / 39,60"	2,133 / 4,693
Pendant U50 L1100 PG	348 091	S250GD Z275 MAC	EN 10346	GS	/	2 / 0,079"	1106 / 43,54"	2,293 / 5,045
Pendant U50 L1200 PG	348 089	S250GD Z275 MAC	EN 10346	GS	/	2 / 0,079"	1206 / 47,48"	2,453 / 5,397

Dimensions in (mm/Inch) :

