





















M1-160  
M2-250

91830AN

x 4




M1-160  
M2-250

**B**

---

D

400 mm




M1-160  
M2-250

---




C

---



400 mm



M250  
M630  
M1600




91830AN



|              |   |   |   |                  |                  |                        |
|--------------|---|---|---|------------------|------------------|------------------------|
|              |   |   |   |                  |                  |                        |
| M250<br>M630 | D | F | — | 400 mm<br>600 mm | 400 mm<br>600 mm | MT7357PC<br>MT7457PC   |
| M250<br>M630 | — | — | D | 400 mm<br>600 mm | 400 mm<br>600 mm | —                      |
|              |   |   |   |                  |                  |                        |
| M250<br>M630 | B | B | B | 400 mm           | 400 mm           | MT7357PC<br>MT7357PC/D |
| M5           | E | E | E | 600 mm           | —                |                        |
|              |   |   |   |                  |                  | MT7457PC<br>MT7457PC/D |


1

4P






2

9061 TR/TN - 9062TR/TN - 9531P13E






3




M250 - M630




M250 - M630




M630




1



2



3



4

