







					
		4044 33	4044 60/61		
I _{pk} (kA)	I _{cw} (kA)	30	15	1600	D
		40	20	1000	
		52	25	800	
		63	30	700	
		73	35	600	
		84	40	500	
		94	45	400	
		105	50	400	

