

XL³400

4 044 36

2

3

15 Nm

1

4 044 38

4 044 39

5

15 Nm

5 Nm

4 044 37

4

D

	A		I _{cn} (kA)	D (mm)
4 044 30	250	4 044 37	5	1600
4 044 31	400		10	1600
			15	1000
			20	800
			25	600

15 Nm

5 Nm

1/4

