

Ortronics Clarity High Density Jack (HDJ) CAT6, T568A/B, White Part No. HDJ6-88



Clarity High Density Jacks (HDJ) unshielded are available in CAT5E, CAT6 and CAT6A, featuring lacing cap termination with icon slot for port ID. Jacks are sold in carton of 20, or bulk pack of 25, termination tool is included with each carton.

## Features & Benefits

Guaranteed Performance levels Lacing Cap Design ETL verified to TIA Category 6a & 6 component specification. No punch tool required, quick termination and installation time. Rear loading Icon compatible, C6a & Cat6 marking on jack face Preferred mounting for panels. Supports 606 designation requirements. **RoHS** compliant Easy to follow universal wiring label Lead free. Quick and user-friendly, eliminates confusion. Center tuned design High density footprint Transparent interface with Clarity 6a & 6 patch cords. Supports 48 port 1RU panel applications. Supports PoE IEEE 802.3af / 802.3at and 802.3bt Type 3 and Type 4

## Specifications

## General Info

Product Line	Ortronics	Color	Cloud White
JPC Number	662875880905	Country Of Origin	Mexico
Application Sector	Commercial/Industrial	Standard	TIA-568.2-D, UL 1863, IEEE 802.3af / 802.3at, 802.3bt Type 3 and Type 4, FCC part 68, Subpart F and IEC-603-7 compliant
Гуре	Jack		

Product Width US	0.63 in	Product Depth US	1.61 in
Product Height US	0.77 in		
Additional Information			
RoHS Conformant	Yes	Product Environmental Profile	Yes
Technical Information			
Compatibility	568A/B	PoE Specs	IEEE 802.3af, 802.3at, 802.3bt Type 1 through 4
Shielded/Unshielded	Unshielded	Gauge	22-26 AWG
Performance Level/Tier	Cat 6	Operating Temperature	-40 + 70 C