

Ortronics Clarity High Density Jack (HDJ) CAT6A, T568A/B, Black Part No. HDJ6A-00

Clarity High Density Jacks (HDJ) unshielded are available in CAT5E, CAT6 and CAT6A, featuring lacing cap termination with icon slot for port ID. Jacks are sold in carton of 20, or bulk pack of 25, termination tool is included with each carton.



## Features & Benefits

Guaranteed Performance levels Lacing Cap Design ETL verified to TIA Category 6a & 6 component specification. No punch tool required, quick termination and installation time. Rear loading Icon compatible, C6a & Cat6 marking on jack face Preferred mounting for panels. Supports 606 designation requirements. **RoHS** compliant Easy to follow universal wiring label Lead free. Quick and user-friendly, eliminates confusion. Center tuned design High density footprint Transparent interface with Clarity 6a & 6 patch cords. Supports 48 port 1RU panel applications. Supports PoE

IEEE 802.3af / 802.3at and 802.3bt Type 3 and Type 4

## Specifications

## General Info

Black
Origin Mexico
Jack
pth US 1.61 in

Product Height US	0.77 in		
Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Compatibility	568A/B	PoE Specs	IEEE 802.3af, 802.3at, 802.3bt Type 1 through 4
Shielded/Unshielded	Unshielded	Gauge	22-26 AWG
Performance Level/Tier	Cat 6a	Operating Temperature	-40 + 70 C