

Bticino S.p.A.


Viale Borri, 231 – 21100 Varese (VA) – ITALY

Item codes: from 387860 to 387865

www.bticino.com - www.legrand.com

TILOK TKM connectors

Straight male connectors




SUMMARY	PAGES
1. Description and applications	1
2. Dimensions and compatibility	1
3. Technical features	1
4. Environmental profile	2
5. Conformity and approvals	2

1. DESCRIPTION AND APPLICATIONS

Straight metal male patented connector with fast coupling system to connect rigid pipes and boxes. Suitable for most applications it ensures the connection of pipes with high mechanical and thermal performances, high resistance to traction and torque and a good resistance to vibration. Used together with TAZ or TAIX conduits and it guarantees an IP68 protection index with a good tightening and a fast patented coupling system. It's the ideal solution for energy, signal or power distribution in industrial, commercial, infrastructures and residential applications.

2. DIMENSIONS AND COMPATIBILITY

Dimensions and packaging:



Item TKM	Conduit	THR	Dimensions [mm]				Pack
	diam. [mm]*		ØPU	СН	L	L1	[pcs]
387860	16	M16	12,5	24,0	26,0	10,0	15
387861	20	M20	16,5	28,0	27,0	11,0	10
387862	25	M25	21,5	33,0	29,0	11,0	10
387863	32	M32	27,0	40,0	30,0	12,5	5
387864	40	M40	35,0	50,0	32,0	13,0	5
387865	50	M50	45,0	59,0	47,0	13,0	3

^{*} External diameter of the pipe

Compatibility:

Conduits TAZ and TAIX series, metal accessories and equipments.





Patent:

All the TILOK connectors have a patented quick system to be coupled with the rigid metal pipes. The patented quick system works without any tools and ensures a protection index IP68 (used with TAZ or TAIX conduits).



3. TECHNICAL FEATURES

Raw material:

Body: nickel plated brass UNI EN 12164 CW 614N with nickel plating $2 \div 5 \, \mu m$.

Gasket: Thermosetting elastomeric.

Resistance to corrosion:

Represents the resistance to corrosion in different environments: all TILOK connectors have been subjected to the corrosion tests.

Resistance to corrosion in neutral saline mist in according to UNI ISO 9227 (pluviometric index 1,8 ml/hours): no signs of corrosion after 192 hours.

Resistance to corrosion in constant dump humidity in according to DIN 50017 SK (conditions: $38~^{\circ}\text{C}$ / $100~^{\circ}\text{F}$ with 100% of relative humidity): no signs of corrosion after 1000 hours.

Technical data sheet: IDP000078EN/01 Updated: 30th October 2014 Created: 30th October 2014

TILOK TKM connectors

Straight male connectors

Operating temperature:


Minimum: -25° C / -13° F Maximum: +150° C / +302° F

Electric properties:

Electric continuity guaranteed.


IP protection index:

IP68 with TAZ and TAIX series conduits.



2 nd digit IP						
Protection against the ingress of liquids						
8	Protection against drops of water falling at up to 15° from the vertical					
	Protection against drops of rain water at up to 60° from the vertical					
0	Protection against sprays of water from all directions					
	Protection against jets of water from all directions					
-01	Protection against jets of water of similar force to heavy seas					
E	Protection against the effects of immersion					
E O	Protection against prolonged effects of immersion under pressure					

Thread types and dimensions:



4. ENVIRONMENTAL PROFILE

Technical data sheet: IDP000078EN/01

All the items identified in this technical sheet respect in terms of concentration of substances and raw materials the European legislations about dangerous and forbidden substances and chemical preparations.

5. CONFORMITY AND APPROVALS

Item codes: from 387860 to 387865



All the items identified in this technical sheet are compliant to all the requirements and the regulations currently in force in the European Union about safety, health and environmental issues.



IMQ mark: items from 387860 to 387865.



Updated: 30th October 2014

RINA mark: items from 387860 to 387865.

For technical documentation, test reports, commercial information or any other needs please refer to the local LEGRAND office.

L7 legrand