
Classia **RW4177 - RA4177 - RG4177**

Shaver sockets



Use

Shaver socket 2P, protected against overloads and direct short-circuits.

Suitable for use with European et American 2-pin plugs.

The mechanism is supplied with rocker plate, to be equipped with support frame and plate.

Range				
Designation	ltem			
Shaver sockets	☐ RW4177			
	RA4177			
	■ RG4177			


Color code:

■ White colour

Aluminum colour

■ Black colour

Overall dimensions (mm)



	Α	В	C	D
4177	45.1	67.3	44.1	13.8

Connection

Terminal type: screw clamp
Terminal capacity: 2 x 2,5 mm² max
Stripping length: 11 mm

Compatible with flexible or rigid cables

Technical characteristics

- Protection index

(considering a complete installation, including cover plate) Penetration by solid bodies/liquid: IP21D

- Mechanical characteristics

Impact test: IK 04

- Material characteristics

Material:

Case and Key cover: PC (Polycarbonate)

Halogen free.

UV resistant.

Self-extinguishing:

 850° C / 30 s for insulating parts holding live parts in place 650° C / 30 s for other parts made of insulating materials

- Electrical characteristics

Nominal input voltage: 230 Vac Nominal input frequency: 50 – 60 Hz Nominal output voltage: 115/230 Vac Maximum output current: 20 VA

- Climatic characteristics

Storage temperature: -10° C to $+70^{\circ}$ C Use temperature: -5° C to $+35^{\circ}$ C

Cleaning

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Caution: Always test before using special cleaning products.

Standards and approvals

Compliance with standards IEC/EN 61558-2-5 Refer to e.catalogue.

