


# LIVING **NOW** Socket outlet 2P+T 16A

# KW4141 - KG4141 - KM4141 - KR4141 - KV4141 KW4141TR - KG4141TR - KM4141TR



#### Use

Socket outlets for: German standard plugs.

# Range


Designation	ltem	Related cover
Socket 2P+E 16A 250 Va.c socket with earth side contacts - shielded tulip contacts	<ul> <li>KW4141</li> <li>KG4141</li> <li>KM4141</li> <li>KR4141</li> <li>KV4141</li> <li>KV4141</li> <li>KW4141TR</li> <li>KG4141TR</li> <li>KG4141TR</li> </ul>	<ul> <li>KW04</li> <li>KG04</li> <li>KM04</li> <li>KR04</li> <li>KV04</li> </ul>

□ White

Black Green

### **Overall dimensions (mm)**

Red





IDP000269\_01-EN

#### Connection

 Terminal type:
 screw clamp

 Terminal capacity:
 2 x 4 mm<sup>2</sup>max

 Stripping length:
 11 mm

 Compatible with flexible or rigid cables

# **Technical characteristics**

#### - Protection index

(considering a complete installation, including cover plate) Penetration by solid bodies/liquid: IP20D considering complete installation

- Mechanical characteristics Impact test: IK 04

# - Material characteristics

Case and Key cover: PC (Polycarbonate)

Halogen free.

UV resistant.

Self-extinguishing:

 $850^\circ$  C / 30 s for insulating parts holding live parts in place  $650^\circ$  C / 30 s for other parts made of insulating materials

## - Electrical characteristics

Voltage: 250 VAC Current: 16 A

## - Climatic characteristics

Storage temperature:  $-10^{\circ}$  C to  $+70^{\circ}$  C Use temperature:  $-5^{\circ}$  C to  $+35^{\circ}$  C

## Cleaning

18/10/2019

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Caution: Always test before using special cleaning products.

#### **Standards and approvals**

Compliance with standards IEC 60884-1. Refer to e.catalogue.