



LIVING

n o w

Socket outlets - American standard

KW4129 - KG4129 - KM4129 KW4188 - KG4188 - KM4188





Use

Socket outlets for: American standard plugs.

Connection

Terminal type: screw clamp
Terminal capacity: 2 x 4 mm² max
Stripping length: 11 mm
Compatible with flexible or rigid cables

Range		
Designation	ltem	Related cover
Socket 2P 15A 127/250 V a.c. shielded holes	☐ KW4129	☐ KW51
	KG4129	KG51
Socket duplex 2P+T 15 A 127/250 V a.c. shielded holes	☐ KW4188	☐ KW52
	KG4188	KG52

Colours code:

 \square White

■ Black
■ Sand

Technical characteristics

- Protection index

(considering a complete installation, including cover plate)
Penetration by solid bodies/liquid: IP20D considering complete installation

reflectation by some bodies/fiquid: 1220b considering complete installation

- Mechanical characteristics

Impact test: IK 04

- Material characteristics

Material:

Case and Key cover: PC (Polycarbonate)

Halogen free.

UV resistant.

Self-extinguishing:

 850° C / 30 s for insulating parts holding live parts in place 650° C / 30 s for other parts made of insulating materials

- Electrical characteristics


Voltage: 127/250 VAC

Current: 16 A

- Climatic characteristics

Storage temperature: -10° C to $+70^{\circ}$ C Use temperature: -5° C to $+35^{\circ}$ C

Overall dimensions (mm)



	A	В	C	D
4128	45.2	44.7	35.3	10
4188	45.2	67	34.4	10

Cleaning

Clean the surface with a cloth.

 $Do \ not \ use \ acetone, \ tar-removing \ cleaning \ agents \ or \ trichloroethylene.$

Caution: Always test before using special cleaning products.

Standards and approvals

Compliance with standards IEC 60884-1 Refer to e.catalogue.

