
KW4141AC - KM4141AC - KG4141AC

N O W

Connected power outlet



Use

Connected socket which can be controlled by a wireless lighting control and/or remotely via your smartphone, tablet or computer.

Can be used to measure instantaneous and total consumption of the connected device, which can be viewed on the Home + Control app.

Built-in protection against electrical overloads, for increased safety.

Installation in box 40 mm deep (minimum), instead of a standard socket outlet. Claw and/or screw fixing.

One-piece mechanism (grid + mechanism).

Range	
Designation	Cat. Nos.
Connected 2P+E socket, with safety shutter. With activity and identification LED indicator and RESET button (hidden) used to return to factory settings. Supplied complete with claws and site protection covers.	

Colours code:

☐ White: KW34M2 ☐ Sand: KM34M2 ☐ Black: KG34M2

Connection

Terminal type: automatic
Terminal capacity: 2 x 2.5 mm²
Stripping length: 11 mm

Technical characteristics

- Mechanical characteristics

Protection against impacts: IK 04 Protection against solid bodies and/or liquids: IP 41

- Material characteristics

Mechanism casing: PC

Grid: 6.6 PC + Galfan steel

Halogen-free UV resistant

Self-extinguishing: 850°C/30 s for insulating parts holding live parts in place.

650°C/30 s for the other insulating components.

- Electrical characteristics

 Voltage:
 110/230 V~

 Current:
 16 A

 Power:
 3680 W max.

 Frequency:
 50/60 Hz

 Standby consumption:
 0.1 mA

Zigbee technology 2.4 GHz to 2.4835 GHz

Power level: REC 70-03: < 20 dBm

Range: 200 m of unobstructed space 10 m between products indoors

- Climate characteristics

Storage temperature: $0^{\circ}\text{C to } +45^{\circ}\text{C}$ Usage temperature: $+5^{\circ}\text{C to } +45^{\circ}\text{C}$

Standards and approvals

 $Compliant\ with\ installation\ and\ manufacturing\ standards.$

See e-catalogue.

The undersigned, BTICINO, declares that the radio-electric equipment type (KW-KM-KG4141AC) complies with directive 2014/53/EU.


The full text of the EU declaration of conformity is available on the following website: www.bticino.it/red






Connected power outlet


Overall dimensions (mm)





Operation

Front view



Legend

- 1. 16 A connected socket outlet
 Extra built-in protection in the event of overloads of more than 16 A
- 2. LED indicator:
 - useful during installation
 - indicator function can be activated in the $\mbox{{\it Home}} + \mbox{{\it Control}}$ app
- 3. RESET button: used to return to factory settings

Cleaning

Clean the surface with a cloth.

 $Do \ not \ use \ acetone, \ tar-removing \ cleaning \ agents \ or \ trichloroethylene.$

Caution: Always test before using special cleaning products.

The plates must not be painted.



