


Classia **KW4177 - KM4177 - KG4177** 

# **Shaver sockets**



#### Use

Shaver socket 2P, protected against overloads and direct short-circuits.

Suitable for use with European et American 2-pin plugs.


The mechanism is supplied with related cover, to be equipped with support frame and plate.

# 

Color code:

☐ White☐ Sand☐ Black

### Overall dimensions (mm)



#### Connection

Terminal type: screw clamp
Terminal capacity: 2 x 2,5 mm² max
Stripping length: 11 mm
Compatible with flexible or rigid cables

### **Technical characteristics**

#### - Protection index

(considering a complete installation, including cover plate) Penetration by solid bodies/liquid: IP21D

## - Mechanical characteristics

Impact test: IK 04

### - Material characteristics

Material:

Case and Key cover: PC (Polycarbonate)

Halogen free.

UV resistant.

Self-extinguishing:

 $850^{\circ}$  C / 30 s for insulating parts holding live parts in place  $650^{\circ}$  C / 30 s for other parts made of insulating materials

### - Electrical characteristics

Nominal input voltage: 230 Vac Nominal input frequency: 50 – 60 Hz Nominal output voltage: 115/230 Vac Maximum output current: 20 VA

## - Climatic characteristics

Storage temperature:  $-10^{\circ}$  C to  $+70^{\circ}$  C Use temperature:  $-5^{\circ}$  C to  $+35^{\circ}$  C

### Cleaning

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Caution: Always test before using special cleaning products.

## Standards and approvals

Compliance with standards IEC/EN 61558-2-5 Refer to e.catalogue.

