


K4040 N O W K4040V12

Pushbutton lightable with nameplate





Use

Rocker control device for lighting and other loads, with nameplate. Back lightable by led 0,5W

Range			
Designation		ltem	
Pushbutton with			
nameplate			
- 1P (NO) 3A 250 Va.c.	μ	K4040	
- 1P (NO) 3A 12V a.c.	μ	K4040V12	

Overall dimensions (mm)





Connection

Terminal type: screw clamp
Terminal capacity: 2 x 2,5 mm² max
Stripping length: 9 mm Compatible
with flexible or rigid cables

Technical characteristics

- Protection index

(considering a complete installation, including cover plate) Penetration by solid bodies/liquid: IP20

- Mechanical characteristics

Impact test: IK 04

- Material characteristics

Material:

Case: PC (Polycarbonate)
Key cover: PC (Polycarbonate)

Halogen free.

UV resistant.

Self-extinguishing:

 850° C / 30 s for insulating parts holding live parts in place 650° C / 30 s for other parts made of insulating materials

- Electrical characteristics

- Voltage: - 250 V a.c./12 V a.c.

-Current: 3A

- Climatic characteristics

Storage temperature: -10° C to $+70^{\circ}$ C Use temperature: -5° C to $+35^{\circ}$ C

Cleaning

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Caution: Always test before using special cleaning products.

Standards and approvals

 $Compliance\ with\ standards\ IEC/EN\ 60669-1.$

Refer to e.catalogue.

