


LIVING
NOW

## **Socket outlets - British Standard**



### Use


Socket outlets: British standard.

### Range

Designation	Cat. No.	Related Cover Codes
British Standard socket 2 P+E	■ K4150	☐ KW50 ☐ KM50 ■ KG50

Colours code: ☐White ☐ Sand ☐ Black

# Overall dimensions (mm)



	Α	В	C	D
K4150	45	45	29	10

#### Connection

Terminal type: screw clamp
Terminal capacity: 2 x 4 mm² max
Stripping length: 9 mm

Compatible with flexible or rigid cables

### **Technical characteristics**

#### - Protection index

(considering a complete installation, including cover plate) Penetration by solid bodies/liquid: IP20D

# - Mechanical characteristics

Impact test: IK 04

## - Material characteristics

Material:

Case and Key cover: PC (Polycarbonate)

Halogen free.

UV resistant.

Self-extinguishing:

 $850^{\circ}$  C / 30 s for insulating parts holding live parts in place  $650^{\circ}$  C / 30 s for other parts made of insulating materials

## - Electrical characteristics

Voltage: 250 V a.c.

Current: 13 A

#### - Climatic characteristics

Storage temperature:  $-10^{\circ}$  C to  $+70^{\circ}$  C Use temperature:  $-5^{\circ}$  C to  $+35^{\circ}$  C

## Cleaning

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Caution: Always test before using special cleaning products.

# Standards and approvals

Compliance with standards IEC 60884-1

Refer to e.catalogue.

